

ArmorStart Power Media
Control Power Shorting Plugs

6-pin/5-used

Shorting Plugs



Specifications


Mechanical	
Coupling Nut	Black epoxy coated zinc
Overmold	Riteflex TPE
Insert	Yellow Riteflex TPE
Contacts	Brass / gold over palladium Nickel
Electrical	
Assembly Rating	600V, 10 A
Environmental	
Enclosure Type Rating	IP67, NEMA 6P, 1200 psi washdown
Operating Temperature	-20...90°C (-4...194°F)

Features

- 6-pin/5-used configuration to prevent mis-wiring with network connectors
- 1/2 inch - 14 NPT threads

Dimensions—mm (inches)

Dimensions are approximate. Illustrations are not drawn to scale.



Product Selection

Shorting Plugs

Configuration	Assembly Rating	Overmold Color	Wiring Diagram	Cat. No.
E-stop In	600V 10 A	Red	<ol style="list-style-type: none"> 1. ← 2. ← N/C 3. ← N/C 4. ← Blank 5. ← N/C 6. ← 	889A-M65SP61
E-stop Out		Black	<ol style="list-style-type: none"> 1. ← N/C 2. ← N/C 3. ← N/C 4. ← Blank 5. ← 6. ← 	889A-M65SP65

Pinout and Color Code

		Face View Pinout	
		6-pin/5-used	
		<p>Female</p>	<p>Male</p>
Color Code		1 Red (+) 2 Black (-) 3 Green (GND)	4 Blank/Not Used 5 Blue (S1) 6 White (S2)