




**AC FULL VOLTAGE STARTERS • Size 0-4 •
NEMA Type 12 Enclosures • Without Control Transformers**



NEMA Size	Dimensions in Inches (mm)								Approx. Shipping Weight in Lbs. (Kg)
	A Wide	B High	C Deep	D	E	F	G	H	
0-1	8 ³ / ₈ (212.7)	12 ⁷ / ₃₂ (310.4)	5 ⁷ / ₈ (149.2)	11 ¹⁵ / ₃₂ (291.3)	2 ¹ / ₂ (63.5)	9 ⁹ / ₃₂ (7.1)	10 ³ / ₈ (263.5)	7 ⁷ / ₁₆ (11.1)	12 (5.4)
2	8 ⁷ / ₈ (225.4)	15 ³ / ₈ (390.5)	5 ¹⁵ / ₁₆ (150.8)	14 ⁵ / ₈ (371.5)	2 ⁵ / ₈ (66.7)	9 ⁹ / ₃₂ (7.1)	13 ¹ / ₂ (342.9)	7 ⁷ / ₁₆ (11.1)	15 ¹ / ₂ (7)
3	12 ¹ / ₈ (308)	22 ⁷ / ₁₆ (569.9)	7 ¹⁵ / ₁₆ (201.6)	21 ⁹ / ₁₆ (547.7)	4 ⁷ / ₁₆ (112.7)	1 ¹ / ₃₂ (8.7)	20 ³ / ₁₆ (512.8)	1 ¹ / ₂ (12.7)	34 (15.3)
4	14 ¹ / ₈ (358.8)	26 (660.4)	9 ¹ / ₁₆ (230.2)	25 ¹ / ₈ (638.2)	5 ⁷ / ₁₆ (138.1)	1 ¹ / ₃₂ (8.7)	23 ²⁵ / ₃₂ (604)	1 ¹ / ₂ (127)	47 ¹ / ₂ (21.4)

NOTE: Dimensions shown in parentheses are in millimeters.

ALLEN-BRADLEY