

PRODUCT PROFILE

ACCESSORIES/BULLETIN 140U

Bulletin 140U Molded Case Circuit Breakers are now available with Type 4/4X (IP66) Rotary Operating Mechanisms and Multi-tap Terminal Lugs that provide 3 or 6 cable terminations per phase.

VARIABLE DEPTH ROTARY OPERATING MECHANISMS

Rockwell Automation introduces new Variable Depth Rotary Operating Mechanism Kits for the Bulletin 140U Molded Case Circuit Breakers. This new line of operating handles and mechanism kits solves the needs of applications that require NEMA 1/3/3R/4/4X/12 ratings. Similar to the Bulletin 194R rotary disconnect handle, this new handle provides highly visible status indication and reset via the operator. The operating handle is available in two colors (Black and Red/Yellow) and with 12 or 21 inch operating rods. The kits are also available for the G-, H-, J-, K-, L- and M-frame Molded Case Circuit Breakers.

MULTI-TAP TERMINAL LUGS

Bulletin 140U Molded Case Circuit Breakers are now available with new Multi-tap Terminal Lugs that allow for the termination of multiple wires from each phase of the circuit breaker thus eliminating the need for a separate distribution terminal block. These lug kits are available with either 3 or 6 cable terminations per phase on H-, J-, and K-frame Molded Case Circuit Breakers. Multi-tap terminal kits include mounting hardware, insulators, and tin-plated aluminum, 3 phase terminal cover connectors to replace 3 mechanical load lugs. The terminal kits are UL listed for copper only cable as used on the load side of the breaker.

NEW ACCESSORIES FOR BULLETIN 140U MOLDED CASE CIRCUIT BREAKERS





PRODUCT SELECTION

Variable Depth Rotary Operating Mechanism Kit

Frame Size	Max depth	Color	Catalog Number
G-100A	12 inches (305 mm)	Red	140U-G-RVM12R
	12 inches (305 mm)	Black	140U-G-RVM12B
H-125A	12 inches (305 mm)	Red	140U-H-RVM12R
	12 inches (305 mm)	Black	140U-H-RVM12B
	21 inches (533 mm)	Red	140U-H-RVM21R
	21 inches (533 mm)	Black	140U-H-RVM21B
	J-250A	12 inches (305 mm)	Red
12 inches (305 mm)		Black	140U-J-RVM12B
21 inches (533 mm)		Red	140U-J-RVM21R
21 inches (533 mm)		Black	140U-J-RVM21B

Frame Size	Max depth	Color	Catalog Number
K-400A	12 inches (305 mm)	Red	140U-K-RVM12R
	12 inches (305 mm)	Black	140U-K-RVM12B
	21 inches (533 mm)	Red	140U-K-RVM21R
	21 inches (533 mm)	Black	140U-K-RVM21B
	L-600A	12 inches (305 mm)	Red
12 inches (305 mm)		Black	140U-L-RVM12B
21 inches (533 mm)		Red	140U-L-RVM21R
	21 inches (533 mm)	Black	140U-L-RVM21B
	M-800A	12 inches (305 mm)	Red
12 inches (305 mm)		Black	140U-M-RVM12B
21 inches (533 mm)		Red	140U-M-RVM21R
21 inches (533 mm)		Black	140U-M-RVM21B

Multi-Terminal Lug Kits

Frame	Wires per terminal	Wire size range per terminal	Catalog number (with terminal cover)	Catalog number (without terminal cover)
H-125A	3	14-2 AWG (2...33 mm ²)	140U-H-MTL3A	140U-H-MTL3AN
	6	14-6 AWG (2...13 mm ²)	140U-H-MTL6A	140U-H-MTL6AN
J-250A	3	14-2 AWG (2...33 mm ²)	140U-J-MTL3A	—
	6	14-6 AWG (2...13 mm ²)	140U-J-MTL6A	—
K-400A	3	12-2/0 AWG (3...67 mm ²)	140U-K-MTL3A	—
	6	14-3 AWG (2...26mm ²)	140U-K-MTL6A	—

www.rockwellautomation.com

Power, Control and Information Solutions Headquarters

Americas: Rockwell Automation, 1201 South Second Street, Milwaukee, WI 53204-2496 USA, Tel: (1) 414.382.2000, Fax: (1) 414.382.4444

Europe/Middle East/Africa: Rockwell Automation, Vorstlaan/Boulevard du Souverain 36, 1170 Brussels, Belgium, Tel: (32) 2 663 0600, Fax: (32) 2 663 0640

Asia Pacific: Rockwell Automation, Level 14, Core F, Cyberport 3, 100 Cyberport Road, Hong Kong, Tel: (852) 2887 4788, Fax: (852) 2508 1846