



Allen-Bradley

Bulletin 855B Round Industrial Beacons

Signaling Solutions...Loud and Clear

Rockwell Automation/Allen-Bradley is announcing the new family of Round Industrial Beacons! This new line of Beacons is available in sizes of 160 mm and 120 mm diameters. Both sizes are available in steady halogen, flashing halogen, strobe, and rotating halogen versions for flexibility in your applications. The 855B Round Industrial Beacons offer a wide range of mounting options, voltages, and colors.

Advantages

- UL Type 4/4X/13, IP65
- Common and modular components
- Flexible mounting options
- 12V AC/DC, 24V AC/DC, 120V AC, and 240V AC available
- Replaceable strobe tube
- cUL listed and CE marked
- Steady, flashing, rotating halogen, and strobe versions available
- User-selectable rotation speed (90 or 180 RPM) on the Rotating version
- 6 colors available



Bulletin Number 855B

Product Profile

**Rockwell
Automation**

120mm Beacon

855BM -
 a **b** **c** **d** **e**

a

BASE TYPE	
Code	Description
S	Surface Mount ❶
N	1/2 inch NPT Conduit Mount
T	25 mm Tube Mount

c

VOLTAGE	
Code	Description
12	12V AC/DC
24	24V AC/DC
10	120V AC
20	240V AC

e

LENS COLOR	
Code	Description
3	Green
4	Red
5	Amber
6	Blue
7	Clear
8	Yellow

b

NETWORK OPTIONS	
Code	Description
Blank	Standard

d

FUNCTION	
Code	Description
DH	Steady Halogen
FH	Flashing Halogen
RH	Rotating Halogen ❷
BR	Strobe ❸

- ❶ Surface Mount Base must be installed with Rough Wall Plate for UL Type 4/4X/13 rating.
- ❷ 120V AC and 240V AC rotating halogen beacons will be available beginning in January, 2004.
- ❸ Available in 24V AC/DC, 120V AC, or 240V AC.

160mm Beacon

855BL -
 a **b** **c** **d** **e**

a

BASE TYPE	
Code	Description
S	Surface Mount ❶
N	1-inch NPT Conduit Mount
T	30 mm Tube Mount

c

VOLTAGE	
Code	Description
12	12V AC/DC
24	24V AC/DC
10	120V AC
20	240V AC

e

LENS COLOR	
Code	Description
3	Green
4	Red
5	Amber
6	Blue
7	Clear
8	Yellow

b

NETWORK OPTIONS	
Code	Description
Blank	Standard

d

FUNCTION	
Code	Description
DH	Steady Halogen
FH	Flashing Halogen
RH	Rotating Halogen ❷
BR	Strobe ❸

- ❶ Surface Mount Base must be installed with Rough Wall Plate for UL Type 4/4X/13 rating.
- ❷ 120V AC and 240V AC rotating halogen beacons will be available beginning in January, 2004.
- ❸ Not available in 12V AC/DC.

www.rockwellautomation.com

Corporate Headquarters
 Rockwell Automation, 777 East Wisconsin Avenue, Suite 1400, Milwaukee, WI, 53202-5302 USA, Tel: (1) 414.212.5200, Fax: (1) 414.212.5201

Headquarters for Allen-Bradley Products, Rockwell Software Products and Global Manufacturing Solutions
 Americas: Rockwell Automation, 1201 South Second Street, Milwaukee, WI 53204-2496 USA, Tel: (1) 414.382.2000, Fax: (1) 414.382.4444
 Europe/Middle East/Africa: Rockwell Automation SA/NV, Vorstlaan/Boulevard du Souverain 36, 1170 Brussels, Belgium, Tel: (32) 2 663 0600, Fax: (32) 2 663 0640
 Asia Pacific: Rockwell Automation, 27/F Citicorp Centre, 18 Whitfield Road, Causeway Bay, Hong Kong, Tel: (852) 2887 4788, Fax: (852) 2508 1846

Headquarters for Dodge and Reliance Electric Products
 Americas: Rockwell Automation, 6040 Ponders Court, Greenville, SC 29615-4617 USA, Tel: (1) 864.297.4800, Fax: (1) 864.281.2433
 Europe/Middle East/Africa: Rockwell Automation, Brühlstraße 22, D-74834 Elztal-Dallau, Germany, Tel: (49) 6261 9410, Fax: (49) 6261 17741
 Asia Pacific: Rockwell Automation, 55 Newton Road, #11-01/02 Revenue House, Singapore 307987, Tel: (65) 6356-9077, Fax: (65) 6356-9011