# 中国国家强制性产品认证证书

**证书编号：**2024010303707411

**认证委托人名称及地址**

Rockwell Automation, Inc.
1201 South Second Street, Milwaukee, WI 53204, USA

**生产者名称及地址**

Rockwell Automation, Inc.
1201 South Second Street, Milwaukee, WI 53204, USA

**生产企业名称及地址**

NOTE Sofia LTD
Varna Str.1 2850 Petrich Bulgaria

**产品名称和系列、型号、规格**

时间继电器
700-FE...; Ui:300V; Uimp:4kV; AC-15: Ue/Ie: 230V/3A; DC-13: Ue/Ie: 24V/2A; Ithe:5A; IP20; 详见附页

**产品标准和技术要求**

GB/T 14048.5-2017

上述产品符合《强制性产品认证实施规则 低压电器 低压元器件》（CNCA-C03-02:2024）的要求，特发此证。

**发证日期：**2025 年 11 月 27 日 **有效期至：**2029 年 07 月 17 日

本证书为变更证书，证书首次颁发日期：2024 年 10 月 22 日

证书信息和有效性可扫描下方二维码或登录发证机构网站查验，
也可在认监委网站（www.cnca.gov.cn）查询。

签发：谢肇煦

中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司

# 中国国家强制性产品认证证书

证书编号：2024010303707411

证书附页：第 1 页 共 1 页

| 700-FE | M | 6 | T | U23 |
|---|---|---|---|---|
| 1 | 2 | 3 | 4 | 5 |

| | |
|---|---|
| 1 | Designates Product Line<br>700-FE – 17.5mm Economy Timing Relay |
| 2 | Designates Function<br>A – On-Delay<br>B – Off-Delay<br>D – One Shot<br>F – Flasher<br>M – Multi-Function (On-Delay, Off-Delay, One Shot, Flasher)<br>Y – Star-delta |
| 3 | Designates Number of Contacts<br>6 – SPDT (DPDT for 700-FEY6QU23 and 700-FEM6TZ12) |
| 4 | Designates Timing Ranges<br>T – 0.05 sec – 100 hours<br>Q – 0.05 sec – 10 minutes |
| 5 | Designates Supply Voltage<br>U23 – 24-48Vdc, 24-240Vac<br>Z12 – 12-240Vac/dc |

本页为证书附页，应与证书主页同时使用。

中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

# CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

**CERTIFICATE NO.:** 2024010303707411

**NAME AND ADDRESS OF THE APPLICANT**

Rockwell Automation, Inc.
1201 South Second Street, Milwaukee, WI 53204, USA

**NAME AND ADDRESS OF THE MANUFACTURER**

Rockwell Automation, Inc.
1201 South Second Street, Milwaukee, WI 53204, USA

**NAME AND LOCATION OF THE FACTORY**

NOTE Sofia LTD
Varna Str.1 2850 Petrich Bulgaria

**PRODUCT NAME,MODEL AND SPECIFICATION**

Timing Relay
700-FE…; Ui:300V; Uimp:4kV; AC-15: Ue:/Ie: 230V/3A; DC-13: Ue:/Ie: 24V/2A; Ithe:5A; IP20;
Refer to appendix

**STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS**

GB/T 14048.5-2017

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C03-02:2024).

**Valid from:** Nov.27,2025 **Valid until:** Jul.17,2029

Date of original issued: Oct.22,2024

The certificate information and validity could be checked by scanning the QR code below or logging in to the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).

**SIGNATURE:** 谢肇煦

中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

# CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

**CERTIFICATE NO. :** 2024010303707411

**Appendix:** Page 1 of 1

| 700-FE | M | 6 | T | U23 |
|---|---|---|---|---|
| 1 | 2 | 3 | 4 | 5 |

| | |
|---|---|
| 1 | Designates Product Line<br>700-FE – 17.5mm Economy Timing Relay |
| 2 | Designates Function<br>A – On-Delay<br>B – Off-Delay<br>D – One Shot<br>F – Flasher<br>M – Multi-Function (On-Delay, Off-Delay, One Shot, Flasher)<br>Y – Star-delta |
| 3 | Designates Number of Contacts<br>6 – SPDT (DPDT for 700-FEY6QU23 and 700-FEM6TZ12) |
| 4 | Designates Timing Ranges<br>T – 0.05 sec – 100 hours<br>Q – 0.05 sec – 10 minutes |
| 5 | Designates Supply Voltage<br>U23 – 24-48Vdc, 24-240Vac<br>Z12 – 12-240Vac/dc |

This page is attached to the certificate and should be used at the same time as the certificate page.

# 中国国家强制性产品认证证书

**证书编号：**2024010303707415

**认证委托人名称及地址**

Rockwell Automation, Inc.
1201 South Second Street, Milwaukee, WI 53204, USA

**生产者名称及地址**

Rockwell Automation, Inc.
1201 South Second Street, Milwaukee, WI 53204, USA

**生产企业名称及地址**

ABB Stotz-Kontakt GmbH
Hauptstrasse 14-16, D-78132 Hornberg,Germany

**产品名称和系列、型号、规格**

时间继电器
700-FS…; Ui:250V, 500V; Uimp:4kV; AC-15: Ue/Ie: 230V/3A; DC-13: Ue/Ie: 24V/2A; Ith:4A; IP20; 详见附页

**产品标准和技术要求**

GB/T 14048.5-2017

上述产品符合《强制性产品认证实施规则 低压电器 低压元器件》（CNCA-C03-02:2024）的要求，特发此证。

**发证日期：**2024 年 10 月 22 日 **有效期至：**2029 年 07 月 17 日

证书信息和有效性可扫描下方二维码或登录发证机构网站查验，
也可在认监委网站（www.cnca.gov.cn）查询。

签发：谢肇煦

中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司

# 中国国家强制性产品认证证书

证书编号：2024010303707415



| 700-FS | M | 7 | U | U23 |
|---|---|---|---|---|
| 1 | 2 | 3 | 4 | 5 |

| | |
|---|---|
| 1 | Designates Product Line<br>700-FS – 22.5mm High Performance Timing Relay |
| 2 | Designates Function<br>A – On-Delay<br>B – Off-Delay<br>M – Multi-Function (On-Delay, Off-Delay, One Shot, Flasher)<br>K – One Shot/Watch Dog<br>Q – True Off-Delay<br>Y – Star-delta |
| 3 | Designates Number of Contacts<br>6 – SPDT (all functions)<br>7 – DPDT (all functions)<br>8 – DPDT (M function) |
| 4 | Designates Timing Ranges<br>Q – 0.05 sec – 10 min<br>U – 0.05 sec – 300 hours |
| 5 | Designates Supply Voltage<br>A40 – 380-440Vac<br>U23 – 24-48Vdc, 24-240Vac<br>U18 – 24-240Vac/dc |

本页为证书附页，应与证书主页同时使用。

中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

# CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

**CERTIFICATE NO.:** 2024010303707415

**NAME AND ADDRESS OF THE APPLICANT**

Rockwell Automation, Inc.
1201 South Second Street, Milwaukee, WI 53204, USA

**NAME AND ADDRESS OF THE MANUFACTURER**

Rockwell Automation, Inc.
1201 South Second Street, Milwaukee, WI 53204, USA

**NAME AND LOCATION OF THE FACTORY**

ABB Stotz-Kontakt GmbH
Hauptstrasse 14-16, D-78132 Hornberg,Germany

**PRODUCT NAME,MODEL AND SPECIFICATION**

Timing Relay
700-FS…; Ui:250V, 500V; Uimp:4kV; AC-15: Ue/Ie: 230V/3A; DC-13: Ue/Ie: 24V/2A; Ith:4A; IP20;
Refer to appendix

**STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS**

GB/T 14048.5-2017

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C03-02:2024).

**Valid from:** Oct.22,2024 **Valid until:** Jul.17,2029

The certificate information and validity could be checked by scanning the QR code below or logging in to the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).

**SIGNATURE:** 谢肇煦

中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

# CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

**CERTIFICATE NO. :** 2024010303707415

**Appendix:** Page 1 of 1

| 700-FS | M | 7 | U | U23 |
|---|---|---|---|---|
| 1 | 2 | 3 | 4 | 5 |

| | |
|---|---|
| 1 | Designates Product Line<br>700-FS – 22.5mm High Performance Timing Relay |
| 2 | Designates Function<br>A – On-Delay<br>B – Off-Delay<br>M – Multi-Function (On-Delay, Off-Delay, One Shot, Flasher)<br>K – One Shot/Watch Dog<br>Q – True Off-Delay<br>Y – Star-delta |
| 3 | Designates Number of Contacts<br>6 – SPDT (all functions)<br>7 – DPDT (all functions)<br>8 – DPDT (M function) |
| 4 | Designates Timing Ranges<br>Q – 0.05 sec – 10 min<br>U – 0.05 sec – 300 hours |
| 5 | Designates Supply Voltage<br>A40 – 380-440Vac<br>U23 – 24-48Vdc, 24-240Vac<br>U18 – 24-240Vac/dc |

This page is attached to the certificate and should be used at the same time as the certificate page.