

855H Recordable Horn Tone Selection Guide




















Allen-Bradley

by ROCKWELL AUTOMATION

Tone Reference No.	Tone Audio Sample	Tone Description
1		340 Hz Continuous
2		800/1000 Hz @ 0.25 s Alternating
3		500/1200 Hz @ 0.3 Hz 0.5 s Slow Whoop
4		800/1000 Hz @ 1 Hz Sweeping
5		2400 Hz Continuous
6		2400/2900 Hz @ 7 Hz Sweeping
7		2400/2900 Hz @ 1 Hz Sweeping
8		500/1200/500 Hz @ 0.3 Hz Sweeping
9		1200/500 Hz @ 1 Hz - DIN / PFEER P.T.A.P.
10		2400/2900 Hz @ 2 Hz Alternating
11		1000 Hz @ 1 Hz Intermittent
12		800/1000 Hz @ 0.875 Hz Alternating
13		2400 Hz @ 1 Hz Intermittent
14		800 Hz 0.25 s on. 1 s off Intermittent
15		800 Hz Continuous
16		660 Hz 150 ms on. 150 ms off Intermittent
17		544 Hz (100 ms) / 440 Hz (400 ms) - NF S 32-001
18		660 Hz 1.8 s on. 1.8 s off Intermittent
19		1.4...1.6 KHz 1 s. 1.6K...1.4 KHz 0.5 s - NFC48-265
20		660 Hz Continuous
21		554 Hz / 440 Hz @ 1 Hz Alternating
22		544 Hz @ 0.875 s Intermittent
23		800 Hz @ 2 Hz Intermittent
24		800/1000 Hz @ 50 Hz Sweeping
25		2400/2900 Hz @ 50 Hz Sweeping
26		Bell
27		554 Hz Continuous
28		440 Hz Continuous
29		800/1000 Hz @ 7 Hz Sweeping
30		300 Hz Continuous
31		660/1200 Hz @ 1 Hz Sweeping
32		Two tone chime

855H Recordable Horn Tone Selection Guide ...continued

Tone Reference No.	Tone Audio Sample	Tone Description
33		745 Hz @ 1 Hz Intermittent
34		1000 & 2000 Hz @ 0.5 s Alternating - Singapore
35		420 Hz @ 0.625 s Australian Alert
36		500-1200 Hz 3.75 s / 0.25 s Australian Evac.
37		1000 Hz Continuous - PFEER Toxic Gas
38		2000 Hz Continuous
39		800 Hz 0.25 s on. 1 s off Intermittent
40		544 Hz (100 mS) / 440 Hz (400 mS) - NF S 32-001
41		Motor Siren - slow rise to 1200 Hz
42		Motor Siren - slow rise to 800 Hz
43		1200 Hz Continuous
44		Motor Siren - slow rise to 2400 Hz
45		1KHz 1 s on. 1 s off Intermittent - PFEER Gen. Alarm

Connect with us.    

rockwellautomation.com

expanding human possibility®

AMERICAS: Rockwell Automation, 1201 South Second Street, Milwaukee, WI 53204-2496 USA, Tel: (1) 414.382.2000, Fax: (1) 414.382.4444

EUROPE/MIDDLE EAST/AFRICA: Rockwell Automation NV, Pegasus Park, De Kleetlaan 12a, 1831 Diegem, Belgium, Tel: (32) 2663 0600, Fax: (32) 2 663 0640

ASIA PACIFIC: Rockwell Automation, Level 14, Core F, Cyberport 3, 100 Cyberport Road, Hong Kong, Tel: (852) 2887 4788, Fax: (852) 2508 1846

UNITED KINGDOM: Rockwell Automation Ltd., Pitfield, Kiln Farm, Milton Keynes, MK11 3DR, United Kingdom, Tel: (44)(1908) 838-800, Fax: (44)(1908) 261-917

Allen-Bradley and expanding human possibility are trademarks of Rockwell Automation, Inc.
Trademarks not belonging to Rockwell Automation are property of their respective companies.

Publication 855H-SG003A-EN-P - January 2023

Copyright © 2023 Rockwell Automation, Inc. All Rights Reserved. Printed in USA.