















Sealing Caps



Mini and Micro Cap

Connector Style	Material	Thread Config.	Dimensions—mm (in)	Cat. No.	Thread Config.	Dimensions—mm (in)	Cat. No.
Mini	Aluminum	External	 <p>7/8 in-16 UN 2 A Threads</p> <p>Gasket</p>	1485A-C1	Internal	 <p>7/8 in-16 UN 2 B Threads</p> <p>Gasket</p>	889A-NCAP
Mini-Plus (7 and 8 pin)	Aluminum	External	 <p>1 in-16 UN 2 A Threads</p> <p>Gasket</p>	889A-NM2CAP	Internal	 <p>1 in-16 UN 2 B Threads</p> <p>Gasket</p>	889A-N2CAP
Mini-Plus (9, 10, and 12 pin)	Aluminum	External	 <p>1 1/8 in-16 UN 2 A Threads</p> <p>Gasket</p>	889A-NM3CAP	Internal	 <p>1 1/8 in-16 UN 2 B Threads</p> <p>Gasket</p>	889A-N3CAP
DC Micro	Aluminum	External	 <p>M12 x 1 Threads</p>	1485A-C3	Internal	 <p>M12 x 1 Threads</p> <p>Gasket</p>	889A-DCAP
	Plastic	External	 <p>M12 x 1 Threads</p>	1485A-M12	—	—	—
AC Micro	Aluminum	External	 <p>1/2 in UNF Threads</p>	889A-RMCAP	Internal	 <p>1/2 in UNF Threads</p> <p>Gasket</p>	889A-RCAP
Pico	Plastic	External	 <p>M8 x 1 Threads</p>	889A-PMCAP	—	—	—
M23	Nickel-plated Brass	External	 <p>M23 x 1 External Thread</p>	889A-MMCAP	Internal	 <p>M23 x 1 External Thread</p>	889A-MCAP

Accessories

Coupling Adaptor/Mounting Accessories

Coupling Adaptors



Coupling Adaptor

Connector Style	Material	Dimensions—mm (in)	Cat. No.
Mini	Aluminum		889A-NADPT
Mini-Plus (7 and 8 pin)			889A-N2ADPT
Mini-Plus (9, 10, and 12 pin)			889A-N3ADPT

Mounting Accessories

Description	Cat. No.
Mounting nuts for 1/2 in-14NPT threaded receptacles are available in bags of 10 pieces	889A-U1NUT-10
Flat, sealing washers for 1/2 in-14NPT threaded receptacles are available in bags of 10 pieces	889A-U1FSL-10