

# PRODUCT PROFILE

## Bulletin 855W

### Wall Mount Signal Lights

#### Advantages

- Compact, diverse functionality
  - Steady LED
  - Flashing LED
  - User selectable sounder tones
- Lens color with matching LEDs provides versatility for diverse applications
  - Green
  - Red
  - Amber
  - Blue
  - Clear
  - Yellow
- Available in two cosmetic cover finishes to coordinate with machine and equipment aesthetics
  - Grey
  - Chrome
- Suitable for use in indoor/outdoor applications or harsh environments due to superior ingress protection rating
  - UL 4/4X/13, IP65
- Available in three voltages to meet the needs of diverse applications
  - 24V AC/DC
  - 120V AC
  - 240V AC



#### Overview

The Allen-Bradley® Bulletin 855W Wall Mount Signal Lights are ideal for multi-status indication of equipment or machinery conditions while saving valuable mounting space and commissioning costs. Up to six different conditions can be indicated (five visual and one audible) which helps create flexibility in applications where total cost of ownership reduction is key.



This product family is specifically targeted towards OEMs, Contractors, and Panel Builders that are looking for a cost-effective solution utilizing state of the art LED technology.

- Ideal for confined spaces where multiple status indication is required
  - Wall mount does not add extra height to machine or equipment
  - Can be mounted either in horizontal or vertical direction
  - All units are 45 mm deep and 90 mm wide
- Easy mounting helps save time and money
  - Wiring via terminal block
  - Selectable sounds options include pulsing and continuous with volume adjustment

*Help meet required standards with Allen-Bradley Wall Mount Signal Lights.*

# Product Selection

Pre-Assembled Wall Mount Signal Lights, Two to Five Light Levels



**a**

Network Option	
Code	Description
Blank	No network option

**b**

Housing Color	
Code	Description
C	Chrome plated
G	Grey

**c**

Voltage	
Code	Description
24	24V AC/DC
10	120V AC
20	240V AC

**d**

Module Type	
Code	Description
Y	Steady LED
L	Flashing LED

**e**

Lens Color	
Code	Description
3	Green
4	Red
5	Amber
6	Blue
7	Clear
8	Yellow

**f**

Sound	
Code	Description
Blank	No sound
P1	Piezo Sounder (continuous/pulsing)

Allen-Bradley and Rockwell Software are trademarks of Rockwell Automation Inc.

[www.rockwellautomation.com](http://www.rockwellautomation.com)

## Power, Control and Information Solutions Headquarters

Americas: Rockwell Automation, 1201 South Second Street, Milwaukee, WI 53204 USA, Tel: (1) 414.382.2000, Fax: (1) 414.382.4444

Europe/Middle East/Africa: Rockwell Automation, Vorstlaan/Boulevard du Souverain 36, 1170 Brussels, Belgium, Tel: (32) 2 663 0600, Fax: (32) 2 663 0640

Asia Pacific: Rockwell Automation, Level 14, Core F, Cyberport 3, 100 Cyberport Road, Hong Kong, Tel: (852) 2887 4788, Fax: (852) 2508 1846