

Bulletin 507/509/513 NEMA Starters

Features and Benefits

- Copper-free cast aluminum alloy
- External and internal surfaces are chromated to enhance protection against corrosion
- External surface is painted to enhance environment protection
- Flexibility of up to five pilot devices for command and indication on door
- Gasket inside cover to guard against moisture and corrosive elements
- Hinged cover helps eliminate lifting, reduces ergonomic concerns and is convenient for installing pilot devices on door
- Breather and drain provision
- Stainless steel quick-release bolts
- Slotted mounting feet for ease of installation
- Lockable operating handle prevents tampering
- Single bolt and V-band on Unilock panels reduce installation time and cost

Certifications and Ratings

- UL Listed / CSA Certified
- UL Classified Enclosures
- Class I, Division 1 & 2, Groups C, D
- Class II, Division 1 & 2, Groups E, F, and G
- 65 kA short circuit rating
- NEMA Type 3R/7-9



Allen-Bradley offers combination and non-combination NEMA starters which provide flexibility and ease of installations. Their compact design and NEMA Type 3R/7-9 rating allow them to be used in indoor or outdoor applications where installation space is at a premium. The robust enclosures are versatile in design and flexible in configuration to suit a variety of applications. These starters are well-suited for:

- Oil and gas refineries
- On-shore and off-shore drilling
- Mining
- Power plants
- Petrochemical processing

Oil and Gas Supply Chain

Hazardous location starters are installed in all areas of the oil and gas distribution chain. Allen-Bradley hazardous locations starters are designed to meet the challenges of these critical environments.



A Upstream

- Exploration
- On/Off-shore
- Production

B Midstream

- Storage
- Processing
- Distribution/Transportation

C Downstream

- Refinery
- Manufacturing



Local Distributor

Visit our website to find your local Distributor.
www.rockwellautomation.com/distributor



Allen-Bradley, LISTEN. THINK. SOLVE. and Rockwell Software are trademarks of Rockwell Automation, Inc. Trademarks not belonging to Rockwell Automation are property of their respective companies.

www.rockwellautomation.com

Power, Control and Information Solutions Headquarters

Americas: Rockwell Automation, 1201 South Second Street, Milwaukee, WI 53204-2496 USA, Tel: (1) 414.382.2000, Fax: (1) 414.382.4444

Europe/Middle East/Africa: Rockwell Automation NV, Pegasus Park, De Kleetlaan 12a, 1831 Diegem, Belgium, Tel: (32) 2 663 0600, Fax: (32) 2 663 0640

Asia Pacific: Rockwell Automation, Level 14, Core F, Cyberport 3, 100 Cyberport Road, Hong Kong, Tel: (852) 2887 4788, Fax: (852) 2508 1846