

# Western Regional Configuration Center

Local Manufacturing for Quick Delivery



## The right product, right when you need it!

The Rockwell Automation® regional configuration centers provide you the flexibility of product customization with local availability. Configure our most common options to your application needs.

### Availability

Products ship within 48 hours

\*See map for approximate transit times

### Flexibility

- Patented snap-together wiring technology
- Comply with regional needs and standards



Western Regional Configuration Center

■ 1 day transit   ■ 2 day transit   ■ 3 day transit

LISTEN.  
THINK.  
SOLVE.®

# Available Products


Get Back On Site Faster

## NEMA Non-combination Starters



### 509 Non-reversing Starter

- UL Type 1, 4/12 (enclosure codes A, J)
- NEMA Sizes 0...4



### 305 Reversing Starter

### 309 Non-reversing Starter

- UL Type 1
- NEMA Sizes 0...1 reversing
- NEMA Sizes 0...2 non-reversing

## NEMA Combination Starters



### 512 Non-reversing Starter with Visible Blade Disconnect Switch

### 513 Non-reversing Starter with Molded Case Circuit Breaker

- UL Type 1, 4/12, 4X (enclosure codes A, F, C)
- NEMA Sizes 0...3

## NEMA Contactor



### 500 Contactor

- UL Type 1 (enclosure code A)
- NEMA Size 0...2

## NEMA Lighting Contactor



### 500L Lighting Contactor

- UL Type 1 (enclosure code A)
- 5...60 A

## IEC Non-combination Starters



### 105-C Reversing Starter

### 109-C Non-reversing Starter

- IP42 (Type 1)
- IP66 (Type 3/4/12)
- 9...85 A (non-reversing)
- 9...37 A (reversing)

## Soft Starters



### 150C, 152C, 153C SMC™-3 Soft Starter

### 150F, 152F, 153F SMC™ Flex Soft Starter

### 150S, 152S, 153S SMC™-50 Soft Starter

- UL Type 1/12/13 (enclosure code J)
- 90...520 A

## Local Distributor

Visit our website to find your local distributor.  
[www.rockwellautomation.com/distributor](http://www.rockwellautomation.com/distributor)



## Product Selection Toolbox

Our powerful range of product selection and system configuration tools assist you in choosing and applying our products.  
[www.rockwellautomation.com/en/e-tools](http://www.rockwellautomation.com/en/e-tools)



\* See ProposalWorks™ tool for catalog number configuration.

Allen-Bradley, Listen.Think.Solve, ProposalWorks, Rockwell Automation and Rockwell Software are trademarks of Rockwell Automation, Inc.

[www.rockwellautomation.com](http://www.rockwellautomation.com)

## Power, Control and Information Solutions Headquarters

Americas: Rockwell Automation, 1201 South Second Street, Milwaukee, WI 53204-2496 USA, Tel: (1) 414.382.2000, Fax: (1) 414.382.4444

Europe/Middle East/Africa: Rockwell Automation NV, Pegasus Park, De Kleetlaan 12a, 1831 Diegem, Belgium, Tel: (32) 2 663 0600, Fax: (32) 2 663 0640

Asia Pacific: Rockwell Automation, Level 14, Core F, Cyberport 3, 100 Cyberport Road, Hong Kong, Tel: (852) 2887 4788, Fax: (852) 2508 1846

Publication CMPNTS-QR003C-EN-P – March 2017

Copyright © 2017 Rockwell Automation, Inc. All Rights Reserved. Printed in USA.