Motor Protection Solutions

Allen-Bradley


Protecting Your Investments






Motor Protection Solutions

The Allen-Bradley[®] line of motor protection devices encompasses a range of simple, single purpose protection to the newer overload technologies featuring diagnostics and Logix integration.






	MachineAlert	Bimetallic	E100	E200	E300	857
Protection Features						
Overload		 	 ✓ 	V	v	 ✓
Phase loss	 ✓ 		v	v	 	~
Ground fault			v	v	 Image: A set of the set of the	~
Current imbalance		v		 	 ✓ 	~
Jam	 ✓ 		v	v	 ✓ 	~
Over/under voltage	 ✓ 			v	 ✓ 	~
Voltage imbalance	 ✓ 			 ✓ 	 ✓ 	~
Over/under power	 ✓ 			v	 Image: A set of the set of the	~
Diagnostics Features						
% Full load amperes			v	 	 Image: A set of the set of the	~
% Thermal capacity utilization			v	 ✓ 	 ✓ 	~
Voltage				v	 	~
Power				V	 	~
Energy				v	 Image: A start of the start of	~
Integration Features	· · · · · · · · · · · · · · · · · · ·					
DeviceLogix™				v	 	
Logix controller					 	 ✓

Feature Comparison

E100 Electronic Overload Relay

The E100 Electronic Overload Relay is the next generation basic-tier electronic overload relay. It has enhanced features to better safeguard your motor protection investments, including increased accuracy and repeatability, a self-powered design with lower heat dissipation, and an aggressive component certification strategy.



5:1 Current Range • Wide FLA range

Optional Accessories

- Ground fault/jam
- Remote reset and/or indication
- Anti-tamper shields
- DIN rail/panel mounting
- External CT configurations

Customizable

The E100 is divided into two offerings, a basic and advanced version, allowing you to customize the device to your application's specific needs.



Reset Adapter



Ground Fault and Jam Protection Accessory



Electronic Remote Reset Accessory

Model Specifications

Bulletin 193, 1EE Model					
Current Range	0.1100 A				
Trip Class	10, 20 Adjustable				
Reset Mode	Manual Only				
Accessories	Reset Adapter, Anti-Tamper Shield, Remote Reset Solenoid, DIN Rail/Panel Adapter				

Bulletin 193/592, 1EF Model					
Current Range	0.1800 A				
Trip Class	10, 15, 20, 30 Adjustable				
Reset Mode	Automatic and Manual				
Accessories	Reset Adapter, Anti-Tamper Shield, Remote Reset Solenoid, DIN Rail/Panel Adapter, Electronic Remote Reset Accessory, GF and Jam Accessory				

Mounting Options



NEMA Motor Starter

with Pass-thru



Features



The E100 Electronic Overload Relay is the newest technology for overload protection, and supports both single- and three-phase operation in a single component.

Accurate, Reliable Performance

- Current measurement-based protection
- Electronic design
- Thermal memory
- · Enhanced phase loss protection

Easy to Select and Apply

- · Straightforward installation
- · Wide adjustment range

Rugged Construction

- Over-molded power connections
- Current transformers
- Latching relay

Application Flexibility

- Isolated contacts
- DIP switch settings

Pass-thru Option

E100 **Supported Remote Reset Methods**



Electro-Mechnanical Solenoid (240V AC, 120V AC, 24V DC)




Electrical Reset & Indication Display (ERID) Module (requires ERR or EGJ)



Electrical Indication Display without Reset Module (requires ERR or EGJ)

E300/E200 Electronic Overload Relay

The E300/E200 Electronic Overload Relays provide a flexible design and advanced intelligence. Real-time diagnostics are transformed into actionable information – maximizing your up-time and protecting your assets.



240V AC 4 IN / 2 OUT

• 120V AC

240V AC

expand out to 4 of the available

I/O modules along with a power supply and operator interface.

Digital I/O modules, plus 4 Analog

Operator station

Module Specifications

Communication Module

193-ECM Features

- EtherNet/IP
 - DeviceNet
 - E200/Parameter Configuration Module (PCM)
 - Includes Single USB Type B interface port

Control Module

193-EIO		I/0		I/O and Protection	
	Control Voltage	Inputs	Relay Outputs	Inputs	Relay Outputs
	110120V AC 50/60 Hz	4	3	2	2
		2	2	-	-
	220240V AC 50/60 Hz	4	3	2	2
		2	2	-	-
	24V DC	6	3	4	2
	24V DC	2	2	-	-

Sensing Module

- 592/193-ESM **Sensing Options:**
 - Voltage/Current/Ground Fault
 - Current/Ground Fault
 - Current
- Current Range: • 0.5...30 A • 6...60 A • 10...100 A • 20...200 A Current transformer solutions

available for applications above 200 A

Mounting Options







DIN Rail Mount Motor Starter

NEMA Motor Starter

IEC Motor Starter



Expansion Analog I/O

- 3 universal inputs/ 1 output
- 4 20 mA
- 0 10V
- RTD
- NTC

- Expansion **Power Supply**
- 120/240V AC
- 24V DC

Diagnostics




The E300/E200 overload relay provides real-time motor diagnostic information to proactively indicate when a motor is having a problem allowing you to efficiently troubleshoot. This information includes:

- Current
- Ground fault current
- Voltage
- Power
- Energy

- % thermal capacity utilization
- Time to trip
- Time to reset
- Trip history
- Trip snapshot

The communication options of the E300/E200 overload relay allow users to view this diagnostic information using the following methods:

- Logix add-on profile
- Embedded web browser
- FactoryTalk[®] View
- Pre-configured Operator Faceplate Objects
- Connected Component Workbench[™] software (E200 only)





Expansion **Operator Station**


- Diagnostic station
- Control station
- Both support copycat feature

22 mm push button cutout



MachineAlert Monitoring Relays

The MachineAlert family of dedicated function motor protection relays offers supplementary protective functions that are easily added to your motor control circuits.






Ideal Applications

- Protects against single phasing during start-up and run-time in motor applications
- Detects incorrect phase sequence to keep the motor from starting
- Detects no-load conditions indicating absence of water in water lubricated pumps
- · Protects motors from over temperature conditions

Bimetallic Overload Relays

The bimetallic thermal overload relays compensate for ambient temperature while providing overload protection and phase-loss sensitivity. They are a cost-effective way to protect your electrical equipment investment.



The 193-T bimetallic overload relays are designed for use with the 100-C contactors and 104-C reversing contactors.



193-K Bimetallic

The 193-K bimetallic overload relays are designed for use with the 100-K miniature contactors and 104-K miniature reversing contactors.

Offers basic motor protection at an economic price




Ideal Applications

Ideal for light industry and low critical process

- Conveyors
- Fans
- Pumps
- VFD-controlled motors
- DC motors

857 Motor/Feeder Protection Relay

The 857 medium/high-voltage motor and feeder protection relay contains the essential protection functions needed to protect feeders, and motors in distribution networks of utilities, heavy industries, power plants and offshore applications.






Functions

This device also includes many programmable functions for various protection and communication situations:

- Ultra-fast arc protection (optional)
- Power quality assessment
- Trip circuit supervision
- Circuit breaker protection
- Complete protection and control

Product Selection Attributes

Diagnostics



Usability



Bimetallic


- Selectable reset mode
- Built-in test/reset button
- Manual trip



E100

- Multiple trip class options
- Selectable reset modes
- Wide current range
- Additional modules for enhanced functionality

Performance





E200

- Wide current range
- Advanced performance
 and diagnostics
- Modularity
- Multiple expansion options

E300

- Wide current range
- Advanced performance and diagnostics
- Modularity
- Multiple expansion options
- Embedded
 communications

Prevent motor failures, protect your investments

Local Distributor

Visit our website to find your local Distributor. www.rockwellautomation.com/distributor

Online Product Directory

Our portfolio of motor protection devices are designed to protect your manufacturing investments. https://ab.rockwellautomation.com/allenbradley/productdirectory.page

The Connected Enterprise

Learn more about how The Connected Enterprise transforms real-time data, from intelligent assets and multi-disciplined control from a plant, or a remote site into actionable information. https://www.rockwellautomation.com/global/capabilities/ connected-enterprise/overview.page

Product Selection Toolbox


rockwellautomation.com -

Our powerful range of product selection and system configuration tools assist you in choosing and applying our products. https://www.rockwellautomation.com/global/support/productselection-configuration/overview.page

Rockwell Automation, Inc. (NYSE:ROK), the world's largest company dedicated to industrial automation, makes its customers more productive and the world more sustainable. Throughout the world, our flagship Allen-Bradley[®] product brands are recognized for innovation and excellence.

AMERICAS: Rockwell Automation, 1201 South Second Street, Milwaukee, WI 53204-2496 USA, Tel: (1) 414.382.2000, Fax: (1) 414.382.4444 EUROPE/MIDDLE EAST/AFRICA: Rockwell Automation NV, Pegasus Park, De Kleetlaan 12a, 1831 Diegem, Belgium, Tel: (32) 2 663 0600, Fax: (32) 2 663 0640 ASIA PACIFIC: Rockwell Automation, Level 14, Core F, Cyberport 3, 100 Cyberport Road, Hong Kong, Tel: (852) 2887 4788, Fax: (852) 2508 1846

Allen-Bradley, CompactLogix, Connected Components Workbench, Expanding human possibility, PanelView, PowerFlex and Rockwell Automation are trademarks of Rockwell Automation, Inc. EtherNet/IP is a trademark of ODVA. Trademarks not belonging to Rockwell Automation are the property of their respective companies.









expanding human possibility[™]