Ref. Certif. No.
NL-72601

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Contactors, safety contactors, reversing contactors, motor starters
Name and address of the applicant	Rockwell Automation, Inc. 1201 South 2nd street, Milwaukee, WI 53204 United States of America
Name and address of the manufacturer	Rockwell Automation, Inc. 1201 South 2nd street, Milwaukee, WI 53204 United States of America
Name and address of the factory Note: *When more than one factory, please report on page 2*	☐ Additional information on page 2 Rockwell Automation SP. Z. O. O. KATOWICE SITE UL. ROZDZIENSKA 49 40-382 KATOWICE Poland
Ratings and principal characteristics	AC-1: (Ue: 200 V - 690 V; Ie: 65 A) AC-3 / AC-4: (Ue: 200 V – 690 V; Ie: 18 A – 38 A) See annex for further ratings.
Trademark (if any)	Allen-Bradley or A-B
Customer's Testing Facility (CTF) Stage used	CTF Stage 3
Model / Type Ref.	100-C30*, 100S-C30*, 104-C30*, 104S-C30* 100-C37*, 100S-C37*, 104-C37*, 104S-C37* 100-C40*, 100S-C40*
Additional information (if necessary may also be reported on page 2)	☐ Additional information on page 2
A sample of the product was tested and found to be in conformity with	IEC 60947-4-1:2009, IEC 60947-4-1:2009/AMD1:2012
As shown in the Test Report Ref. No. which forms part of this Certificate	2255966.50

This CB Test Certificate is issued by the National Certification Body

DEKRA Certification B.V.
Meander 1051, NL-6825 MJ Arnhem, Netherlands

DEKRA

Date: 2021-05-17

Signature: David Huang

Table Ratings: A-B: 100(S)-C30* / 100(S)-C37*, 104(S)-C30* / 104(S)-C37*, 100(S)-C40*

Value:			Contactor Size:			
			100(S)-C30*	100(S)-C37* 100(S)-C40*	104(S)-C30*	104(S)-C37*
Ith	Ui = 690V	[A]	65	65	65	65
AC-1:						
	690V	[A]	65	65	65	65
AC-3:						
Ie	200V	[A]	25.3	32.2	25.3	32.2
	230V	[A]	35	38	35	38
	240V	[A]	35	38	35	38
	400V	[A]	30	37	30	37
	415V	[A]	30	37	30	37
	440V	[A]	30	37	30	37
	460V	[A]	27	34	27	34
	500V	[A]	25	30	25	30
	575V	[A]	27	32	27	32
	690V	[A]	18	21	18	21
Pe	230V	[kW]	10	11	10	11
	240V	[kW]	10	11	10	11
	400V	[kW]	15	18.5	15	18.5
	415V	[kW]	15	20	15	20
	440V	[kW]	15	20	15	20
	460V	[kW]	15	20	15	20
	500V	[kW]	15	20	15	20
	575V	[kW]	15	18.5	15	18.5
	690V	[kW]	15	18.5	15	18.5
AC-4:						
Ie	200V	[A]	25.3	32.2	25.3	32.2
	230V	[A]	35	38	35	38
	240V	[A]	35	38	35	38
	400V	[A]	30	37	30	37
	415V	[A]	30	37	30	37
	440V	[A]	30	37	30	37
	460V	[A]	27	34	27	34
	500V	[A]	25	30	25	30
	575V	[A]	27	32	27	32
	690V	[A]	18	21	18	21
Pe	230V	[kW]	10	11	10	11
	240V	[kW]	10	11	10	11
	400V	[kW]	15	18.5	15	18.5
	415V	[kW]	15	20	15	20
	440V	[kW]	15	20	15	20
	460V	[kW]	15	20	15	20
	500V	[kW]	15	20	15	20
	575V	[kW]	15	18.5	15	18.5
	690V	[kW]	15	18.5	15	18.5

Table Ratings: A-B: 100(S)-C30* / 100(S)-C37*, 104(S)-C30* / 104(S)-C37*, 100(S)-C40* (continued)

Value:			Contactor Size:			
			100(S)-C30*	100(S)-C37* 100(S)-C40*	104(S)-C30*	104(S)-C37*
AC-4:			AC-4: at approximately 200'000 operations			
Ie	230V	[A]	12	14	12	14
	240V	[A]	12	14	12	14
	400V	[A]	12	14	12	14
	415V	[A]	12	14	12	14
	500V	[A]	12	14	12	14
	690V	[A]	12	14	12	14
Pe	230V	[kW]	3	3.7	3	3.7
	240V	[kW]	3	4	3	4
	400V	[kW]	5.5	6.3	5.5	6.3
	415V	[kW]	5.5	6.3	5.5	6.3
	500V	[kW]	7.5	7.5	7.5	7.5
	690V	[kW]	10	11	10	11

* may be followed by suffix/suffixes and or letter/letters or any combination thereof
Electromagnetic Coil:
Coil Type: AC = conventional or electronically controlled DC = electronically controlled
Ue = Voltage Ue 230 Vac / 690 Vac, 50/60 Hz
Note 1: According to clause 9.3.2 of IEC 60947-4-1 tests performed at 50 Hz are deemed to cover 60 Hz applications and vice-versa.