# 中国国家强制性产品认证证书

**证书编号：**2024010303707430

**认证委托人名称及地址**

Rockwell Automation, Inc.
1201 South Second Street, Milwaukee, WI 53204, USA

**生产者名称及地址**

Rockwell Automation, Inc.
1201 South Second Street, Milwaukee, WI 53204, USA

**生产企业名称及地址**

ABB France
11 Rue d'Arsonval 69680, Chassieu, FRANCE

**产品名称和系列、型号、规格**

控制继电器
700-EF..., 700S-EF...; 详见附页

**产品标准和技术要求**

GB/T 14048.5-2017

上述产品符合《强制性产品认证实施规则 低压电器 低压元器件》（CNCA-C03-02:2024）的要求，特发此证。

**发证日期：**2024 年 10 月 22 日 **有效期至：**2029 年 07 月 11 日

证书信息和有效性可扫描下方二维码或登录发证机构网站查验，
也可在认监委网站（www.cnca.gov.cn）查询。

签发：谢肇煦

中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司

# 中国国家强制性产品认证证书

证书编号：2024010303707430



Ui：690V；
Uimp：6kV；
Ith：16A；
AC-15：Ue/Ie： 24-127V/6A，220-240V/4A，380-440V/3A，500-690V/2A；
DC-13：Ue/Ie：24V/6A，48V/4A,72V/1A，110-125V/0.55A,220-250V/0.27A，
400V/0.15A，500V/0.13A，600V/0.1A；
Us：Normal Power 正常功耗:
AC24-60V 50/60Hz，AC24-60V 50/60Hz /20-60V DC，AC48-130V 50/60Hz -DC，
AC100-250V 50/60Hz-DC， AC250-500V 50/ 60Hz-DC；
Low Power 低功耗:
12-20V DC，AC24-60V 50/60Hz /20-60V DC，AC48-130V 50/60Hz-DC，
AC100-250V 50/60Hz-DC，24V DC；
外壳防护等级：IP20

本页为证书附页，应与证书主页同时使用。

中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE
中国质量认证中心有限公司
http://www.cqc.com.cn 北京市丰台区南四环西路188号九区5号楼 100070 电话：+86 10 83886666

# 中国国家强制性产品认证证书

证书编号：2024010303707430



## 1. 型号的解释(Explanation of Catalog No.)：

| 700-E | | F | | 400 | | KJ | | C |
|---|---|---|---|---|---|---|---|---|
| 1 | | 2 | | 3 | | 4 | | 5 |

| | | |
|---|---|---|
| **1** | **Name of series** | |
| | 700-E | IEC Contactor Relay |
| | 700S-E | IEC Safety Contactor Relay |
| **2** | **Terminal Type** | |
| | F | Screw terminal |
| | RF | Spring clamp (Push-in) terminal |
| **3** | **Contact Configuration** | |
| | 220 | 2 NO / 2 NC contacts |
| | 310 | 3 NO / 1 NC contacts |
| | 400 | 4 NO / 0 NC contacts |
| | 440 | 4 NO / 4 NC contacts |
| | 530 | 5 NO / 3 NC contacts |
| | 620 | 6 NO / 2 NC contacts |
| **4** | **Coil voltage code** | |
| | EQ | 12-20V DC (low power consumption) |
| | EJ | 24-60V AC, 20-60V DC (low power consumption) |
| | QJ | 24V DC (low power consumption, fast drop-out) |
| | KJ | 24-60V AC / 20-60V DC |
| | KY | 48-130V AC/DC |
| | KD | 100-250V AC/DC |

本页为证书附页，应与证书主页同时使用。

# 中国国家强制性产品认证证书

证书编号：2024010303707430



| | | |
|---|---|---|
| | KN | 250-500V AC/DC |
| **5** | **Contacts** | |
| | Blank | No contact block provided |
| | C | Contact block permanently fixed |

本页为证书附页，应与证书主页同时使用。

中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心有限公司

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

# CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

**CERTIFICATE NO.:** 2024010303707430

**NAME AND ADDRESS OF THE APPLICANT**

Rockwell Automation, Inc.
1201 South Second Street, Milwaukee, WI 53204, USA

**NAME AND ADDRESS OF THE MANUFACTURER**

Rockwell Automation, Inc.
1201 South Second Street, Milwaukee, WI 53204, USA

**NAME AND LOCATION OF THE FACTORY**

ABB France
11 Rue d'Arsonval 69680, Chassieu, FRANCE

**PRODUCT NAME,MODEL AND SPECIFICATION**

Control Relay
700-EF..., 700S-EF...;  Refer to the appendix

**STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS**

GB/T 14048.5-2017

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C03-02:2024).

**Valid from:** Oct.22,2024  **Valid until:** Jul.11,2029

The certificate information and validity could be checked by scanning the QR code below or logging in to the website of the issuing authority, or on the website of the CNCA (www.cnca.gov.cn).

**SIGNATURE:** 谢肇煦

中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE CO., LTD.

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

# CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

**CERTIFICATE NO. :** 2024010303707430



Ui：690V；
Uimp：6kV；
Ith：16A；
AC-15：Ue/Ie： 24-127V/6A，220-240V/4A，380-440V/3A，500-690V/2A；
DC-13：Ue/Ie：24V/6A，48V/4A,72V/1A，110-125V/0.55A,220-250V/0.27A，
400V/0.15A，500V/0.13A，600V/0.1A；
Us：Normal Power:
AC24-60V 50/60Hz，AC24-60V 50/60Hz /20-60V DC，AC48-130V 50/60Hz -DC，
AC100-250V 50/60Hz-DC， AC250-500V 50/ 60Hz-DC；
Low Power:
12-20V DC，AC24-60V 50/60Hz /20-60V DC，AC48-130V 50/60Hz-DC，
AC100-250V 50/60Hz-DC，24V DC；
IP20

This page is attached to the certificate and should be used at the same time as the certificate page.

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

# CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

**CERTIFICATE NO. :** 2024010303707430



## 1. 型号的解释(Explanation of Catalog No.):

| 700-E | | F | | 400 | | KJ | | C |
|---|---|---|---|---|---|---|---|---|
| 1 | | 2 | | 3 | | 4 | | 5 |

| | | |
|---|---|---|
| **1** | **Name of series** | |
| | 700-E | IEC Contactor Relay |
| | 700S-E | IEC Safety Contactor Relay |
| **2** | **Terminal Type** | |
| | F | Screw terminal |
| | RF | Spring clamp (Push-in) terminal |
| **3** | **Contact Configuration** | |
| | 220 | 2 NO / 2 NC contacts |
| | 310 | 3 NO / 1 NC contacts |
| | 400 | 4 NO / 0 NC contacts |
| | 440 | 4 NO / 4 NC contacts |
| | 530 | 5 NO / 3 NC contacts |
| | 620 | 6 NO / 2 NC contacts |
| **4** | **Coil voltage code** | |
| | EQ | 12-20V DC (low power consumption) |
| | EJ | 24-60V AC, 20-60V DC (low power consumption) |
| | QJ | 24V DC (low power consumption, fast drop-out) |
| | KJ | 24-60V AC / 20-60V DC |
| | KY | 48-130V AC/DC |
| | KD | 100-250V AC/DC |

This page is attached to the certificate and should be used at the same time as the certificate page.

本翻译文件不具有法律效力，
不得单独使用
This translated document
does not have legal validity and
cannot be used in isolation

# CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

**CERTIFICATE NO. :** 2024010303707430



| | | |
|---|---|---|
| | KN | 250-500V AC/DC |
| **5** | **Contacts** | |
| | Blank | No contact block provided |
| | C | Contact block permanently fixed |

This page is attached to the certificate and should be used at the same time as the certificate page.