Type-examination certificate no. E 7278.e

Object:	relay
Mark:	Allen-Bradley
Type designation:	700S-EF* (safety contactor relay) 100-EF*01* /04* /10* /11* /13* /22* /31* /40* (auxiliary switches, front-mounted) *Various configuration options as specified by the manufacturer Auxiliary switches, front-mounted are firmly connected to the safety contactor relay at the factory.
Technical details concerning safety:	The product meets the requirements of IEC 60947-5-1:2016. Details concerning mechanically linked contact elements according to IEC 60947-5-1, Annex L, useful life B10 and reliability MTTF see supplementary sheet 1/1.
Manufacturer's address:	Rockwell Automation 1201 South Second Street Milwaukee, WI 53204, USA
Address of applicant:	Rockwell Automation Switzerland GmbH Industriestrasse 20 CH-5000 Aarau
Special conditions, enclosures:	See supplementary sheet 1/1
Expires on:	31 March 2027

The prototype examined corresponds to the essential requirements of Directive 2014/35/EU and the amendments of the European Parliament and of the Council of 26 February 2014 on the harmonisation of the laws of the Member States relating to the making available on the market of electrical equipment designed for use within certain voltage limits.
This certificate is valid in conjunction with the general conditions listed on the back and any possible enclosures mentioned above.

Place and date:
Lucerne, 3 March 2022

Suva
Accredited Certification Body SCESp 0008
Technology Sector

The Safety Engineer
Urs Bühlmann

Head of Certification
Guido Schmitter

Supplementary sheet to Certificate no. E 7278.e **Lucerne, 3 March 2022**
Page 1 / 1

In context with this type-examination certificate the meaning of the term mechanically linked contacts is as follows:
If any NO contact is closed, none of the NC contacts is closed. If any NC contact is closed, none of the NO contacts is closed. (IEC 60947-5-1, Annex L)

In order to prevent manual operation in safety-relevant parts of control systems, protective covers have to be used.

Details concerning useful life B10 according to IEC 60947-5-1, Annex N:

Type	B10	B10d	Conditions
700S-EF*	1'000'000	2'000'000	AC-15, 2 A, 240V
700S-EF*	10'000'000	20'000'000	Mechanical lifetime

Mechanical lifetime: operation without load

Details on the reliability of the electronic components according to SN 29500:

Type	MTTF	MTTFd
700S-EF*	233 years	2987 years

These values apply to all voltage variants of the electronically controlled coils.

General conditions

This certificate is valid for the product or product category bearing the trademark and type shown on the front page. In order to guarantee its compliance with the essential health and safety requirements of the directive or regulation stated on the front page, each product or product category must be marked in accordance with the requirements of the directive or regulation stated on the front page and its amendments.

Under the trademark and type designation stated on the front page, the manufacturer or supplier undertakes to deliver only products which, in all aspects that may influence their safety, satisfy the prerequisites for this certificate exactly. This certificate automatically becomes invalid if this condition is not fulfilled.

When assessing the product or product category stated on the front page, it has been assumed that its design and manufacture correspond to the recognized state of the art.

With regard to the operating and servicing instructions supplied with the product, we refer to the requirements of the directive or regulation stated on the front page.

If organizational measures are required to guarantee safety, they must be made known to the buyer and the user and included in the operating and servicing instructions.

The manufacturer is obliged to report to the certification body any complaints regarding the product or product category described on the front page as well as the remedying of faults without delay.

With regard to the area of application, placing on the market and putting into service, free passage of goods, conformity assessment procedures and CE marking, the conditions of the directive or regulation stated on the front page must be complied with.

Reference to this certificate in quotations, brochures, advertisements or other publicity media may only be made if accompanied by its number.

Upon request, the term of validity of the certificate is extended if the product or product category with the relevant conditions of use continues to fulfil the applicable health and safety protection requirements.

However, if new experience or findings indicate that adequate safety cannot be guaranteed or if the product or product category no longer corresponds to the latest state of the art, the certificate can be cancelled by Suva's certification body at any time.

Certification Body SCESp 0008; European notified body, identification number 1246
Suva, Technology Sector, P. O. Box 4358, CH-6002 Lucerne
Phone +41 (0)41 419 61 31, Fax +41 (0)41 419 58 70
www.suva.ch/certification-e

AS 283.e – 06.18 CE 93-11.e