Déclaration De Conformité Du Maroc

Produit:	***Stack Lights***

Nom et adresse du fabricant: ***Rockwell Automation, Inc.*** ***1201 South 2nd Street*** ***Milwaukee, WI 53204*** ***USA***	*Nom et adresse du représentant autorisé:* ***Rockwell Automation B.V.*** ***Rivium Promenade 160*** ***2909 LM Capelle aan den Ijssel*** ***The Netherlands***

La présente déclaration de conformité est établie sous la seule responsabilité du fabricant.

Objet de la declaration:	***Allen-Bradley 855T Series*** *(faire référence à la liste ci-jointe des numéros de catalogue)*

L'objet de la déclaration décrit ci-dessus est conforme aux Ordonnance(s) suivantes du Ministre de l'Industrie, du Commerce, de l'Investissement et de l'Économie numérique:

Arrêté ministériel n° 6404-15 du 1 er muharram 1437 (15 octobre 2015)	*Équipements électriques destinés à être utilisés sous certaines limites de tension*
Arrêté ministériel n° 6404-15 du 29 ramadan 1436 (16 juillet 2015)	*Compatibilité électromagnétique des équipements*

Références des normes harmonisées pertinentes appliquées ou des autres spécifications techniques par rapport auxquelles la conformité est déclarée:

NM EN 60947-5-1	*2014*	*Appareillage à basse tension – Partie 5-1: Appareils et éléments de commutation pour circuits de commande – Appareils électromécaniques pour circuits de commande*

Signé pour et au nom du fabricant mentionné ci-dessus:

Lieu et date de délivrance:	*Milwaukee, WI USA*	*31-Jul-2020*
Nom, fonction:	*Daniel L. Nachtigall, Technical Leader – Product Compliance Engineering*	
Signature:		

Numéro de catalogue	*Séries* [1]	*La description*
855T-xxxNx		*Incandescent light modules per Nomenclature*
855T-xxxLx		*LED light modules per Nomenclature*
855T-xxxRx		*Strobe light modules per Nomenclature*
855PS-Bxxx22		*Panel-mount strobe alarm per Nomenclature*
855T-xxxCx		*Combination light/sound modules per Nomenclature*
855T-xxxA1		*Transducer-style sound modules per Nomenclature*
855T-xxxA3		*Piezo-style sound modules per Nomenclature*
855T-xxx		*Standard base modules per Nomenclature*
855T-Bxxx		*Connection boxes per Nomenclature*
855Tx-xxxyy		*Pre-assembled stack lights per Nomenclature*

1) Les produits du niveau de série indiqué, ainsi que les niveaux de série suivants, sont certifiés. Si aucune lettre ou chiffre de série n'est donné, toutes les séries sont certifiées.

NOMENCLATURE:

Incandescent, LED, and Strobe Light Modules:

855T	-	B	10	FN	4
1		2	3	4	5

1	Designates Product Line 855T – 70mm Control Tower™ stack light		
2	Designates Housing Colour B – Black G – Grey		
3	Designates Voltage Rating 00 – 0 to 250 V AC/DC (only for Module Type XN) 12 – 12 V AC/DC 24 – 24 V AC/DC 10 – 120 V AC 20 – 240 V AC		
4	Designates Module Type <u>Incandescent</u> XN – Steady incandescent, no-lamp option DN – Steady incandescent FN – Flashing incandescent	<u>LED</u> TL – Steady LED GL – Flashing LED RL – Rotating LED	<u>Strobe</u> BR – Strobe
5	Designates Light/Lens Colour A single digit is used to denote colour		

Single/Two Circuit Combined Light/Sound Modules:

855T	-	B	10	DC	3
1		2	3	4	5

1	Designates Product Line 855T – 70mm Control Tower™ stack light
2	Designates Housing Colour B – Black G – Grey
3	Designates Voltage Rating 12 – 12 V AC/DC 24 – 24 V AC/DC 10 – 120 V AC 20 – 240 V AC
4	Designates Module Type

	DC – Single circuit steady incandescent with sound DD – Two circuit steady incandescent with sound FC – Flashing incandescent with sound	TC – Steady LED with sound GC – Flashing LED with sound BC – Strobe with sound
5	Designates Light/Lens Colour A single digit is used to denote colour	

MODEL NOMENCLATURE (CONT):

Sound Modules:

855T	-	B	10	SA1
1		2	3	4

1	Designates Product Line 855T – 70mm Control Tower™ stack light
2	Designates Housing Colour B – Black G – Grey
3	Designates Voltage Rating 12 – 12 V AC/DC 24 – 24 V AC/DC 10 – 120 V AC 20 – 240 V AC
4	Designates Module Type SA1 – Single-tone, transducer-style sound module TA1 – Dual-tone, transducer-style sound module SA2 – Single-tone/single circuit, piezo-style sound module TA2 – Dual-tone/dual circuit, piezo-style sound module SA3 – Single-circuit, piezo-style sound module TA3 – Dual-circuit, piezo-style sound module

Standard Base Modules:

855T	-	B	PM	C
1		2	3	4

1	Designates Product Line 855T – 70mm Control Tower™ stack light		
2	Designates Housing Colour B – Black G – Grey		
3	Designates Base Mounting Type CB – Surface, 1/2 in. NPT SB – Surface mount, PG16 RB – Surface mount, M20 VM – Vertical TM – 25 mm diameter tube	PM10 – 10 cm aluminium pole PM25 – 25 cm aluminium pole PM40 – 40 cm aluminium pole SPM10 – 10 cm stainless steel pole SPM25 – 25 cm stainless steel pole	SPM40 – 40 cm stainless steel pole SPM60 – 60 cm stainless steel pole SPM80 – 80 cm stainless steel pole MM10 – 10 cm On-Machine MM25 – 25 cm On-Machine MM40 – 40 cm On-Machine
4	Designates Cap Option Blank – No cap C – Cap included		

Pole Connection Boxes:

855T	-	B	SMP
1		2	3

1	Designates Product Line 855T – 70mm Control Tower™ stack light

2	Designates Housing Colour B – Black
3	Designates Connection Box Mounting Type SMP – Surface, PG16 SMR – Surface, M20 SMN – Surface, 1/2 in. NPT VMP – Vertical, PG16 VMR – Vertical, M20 MMP – Magnet, PG16 MMR – Magnet, M20 MMN – Magnet, 1/2 in. NPT

MODEL NOMENCLATURE (CONT):

Pre-Assembled Tower Lights:

855T	C	-	B	10	Y	3
1	2		3	4	5	6
					See Note	

1	Designates Product Line 855E – 50mm Control Tower™ stack light
2	Designates Base Type C – Surface mount, 1/2 in. NPT S – Surface mount, PG16 V – Vertical mount M – 25 mm tube mount P – 10 cm pole mount E – 25 cm pole mount
3	Designates Housing Colour B – Black G – Gray
4	Designates Voltage Rating 12 – 12 V AC/DC 24 – 24 V AC/DC 10 – 120 V AC 20 – 240 V AC
5	Designates Module Type D – Steady incandescent F – Flashing incandescent Y – Steady LED L – Flashing LED B – Strobe P – Piezo sound alarm, pulsing tone Q – Dual circuit piezo sound alarm
6	Designates Lens Colour/Sound 1 – Sound Any number 2 through 9 may be used to denote lens colour

NOTE: Suffixes 5 and 6 may be repeated for a maximum of five (5) modules