

Packing Contents

Original Instructions



Allen-Bradley

by ROCKWELL AUTOMATION

FLEXHA 5000 Bank Expansion Bases, Left and Right

Catalog Numbers 5015-BEBLXT, 5015-BEBRXT

IMPORTANT FLEXHA 5000™ Bank Expansion Bases are part of a FLEXHA 5000 I/O system. There are two types--Bank Expansion Base, Left (catalog number 5015-BEBLXT) and Bank Expansion Base, Right (catalog number 5015-BEBRXT).
The system is designed so that individual components can be installed and removed independent of each other. This publication only includes information about the Bank Expansion Bases. For more information on how to install a complete FLEXHA 5000 I/O system, see the FLEXHA 5000 System Installation Instructions, publication [5015-IN001](#).

FLEXHA 5000 Bank Expansion Bases connect the system backplane communication and power from one bank to another through pairs of Backplane Communication Extension cables, catalog number 5015-BECCOMXT, and Backplane Power Extension cables, catalog number 5015-BECPWRXT.

- **Bank Expansion Base, Left** - You can install this base on an Adapter Bank or an I/O Bank.
- **Bank Expansion Base, Right** - You can only install this base on an I/O Base.

IMPORTANT You can install a maximum of two Bank Expansion Bases, Left and Bank Expansion Bases, Right, across a maximum of three banks in a system.

Before You Begin

Before you install the Bank Expansion Bases, at minimum, you must complete the following:

- Install the mounting plates.
- Install the Adapter Bank.

IMPORTANT You can only mount the Adapter base in the horizontal orientation.
However, it cannot be installed in a horizontal flat, that is, facing the sky, orientation.

The example described in this document describes a Bank Expansion Base, Left installed next to an I/O base in the Adapter Bank. However, you can install the Bank Expansion Base, Left, to an Adapter Base or an I/O Base in the Adapter Bank.

- Install at least one I/O Bank, if necessary.



ATTENTION: Read this document and the documents listed in the Additional Resources section about installation, configuration and operation of this equipment before you install, configure, operate or maintain this product. Users are required to familiarize themselves with installation and wiring instructions in addition to requirements of all applicable codes, laws, and standards.

Activities including installation, adjustments, putting into service, use, assembly, disassembly, and maintenance are required to be carried out by suitably trained personnel in accordance with applicable code of practice. If this equipment is used in a manner not specified by the manufacturer, the protection provided by the equipment may be impaired.

注意：在安装、配置、操作和维护本产品前，请阅读本文档以及“其他资源”部分列出的有关设备安装、配置和操作的相应文档。除了所有适用规范、法律和标准的相关要求之外，用户还必须熟悉安装和接线说明。

安装、调整、投运、使用、组装、拆卸和维护等各项操作必须由经过适当训练的专业人员按照适用的操作规范实施。

如果未按照制造商指定的方式使用该设备，则可能会损害设备提供的保护。

ATENCIÓN: Antes de instalar, configurar, poner en funcionamiento o realizar el mantenimiento de este producto, lea este documento y los documentos listados en la sección Recursos adicionales acerca de la instalación, configuración y operación de este equipo. Los usuarios deben familiarizarse con las instrucciones de instalación y cableado y con los requisitos de todos los códigos, leyes y estándares vigentes.

El personal debidamente capacitado debe realizar las actividades relacionadas a la instalación, ajustes, puesta en servicio, uso, ensamble, desensamble y mantenimiento de conformidad con el código de práctica aplicable. Si este equipo se usa de una manera no especificada por el fabricante, la protección provista por el equipo puede resultar afectada.

ATENÇÃO: Leia este e os demais documentos sobre instalação, configuração e operação do equipamento que estão na seção Recursos adicionais antes de instalar, configurar, operar ou manter este produto. Os usuários devem se familiarizar com as instruções de instalação e fiação além das especificações para todos os códigos, leis e normas aplicáveis.

É necessário que as atividades, incluindo instalação, ajustes, colocação em serviço, utilização, montagem, desmontagem e manutenção sejam realizadas por pessoal qualificado e especializado, de acordo com o código de prática aplicável.

Caso este equipamento seja utilizado de maneira não estabelecida pelo fabricante, a proteção fornecida pelo equipamento pode ficar prejudicada.

ВНИМАНИЕ: Перед тем как устанавливать, настраивать, эксплуатировать или обслуживать данное оборудование, прочитайте этот документ и документы, перечисленные в разделе «Дополнительные ресурсы». В этих документах изложены сведения об установке, настройке и эксплуатации данного оборудования. Пользователи обязаны ознакомиться с инструкциями по установке и прокладке соединений, а также с требованиями всех применимых норм, законов и стандартов.

Все действия, включая установку, наладку, ввод в эксплуатацию, использование, сборку, разборку и техническое обслуживание, должны выполняться обученным персоналом в соответствии с применимыми нормами и правилами.

Если оборудование используется не предусмотренным производителем образом, защита оборудования может быть нарушена.

注意：本製品を設置、構成、稼働または保守する前に、本書および本機器の設置、設定、操作についての参考資料の該当箇所に記載されている文書に目を通してください。ユーザは、すべての該当する条例、法律、規格の要件に加えて、設置および配線の手順に習熟している必要があります。

設置調整、運転の開始、使用、組立て、解体、保守を含む諸作業は、該当する実施規則に従って訓練を受けた適切な作業員が実行する必要があります。

本機器が製造メーカーにより指定されていない方法で使用されている場合、機器により提供されている保護が損なわれる恐れがあります。

ACHTUNG: Lesen Sie dieses Dokument und die im Abschnitt „Weitere Informationen“ aufgeführten Dokumente, die Informationen zu Installation, Konfiguration und Bedienung dieses Produkts enthalten, bevor Sie dieses Produkt installieren, konfigurieren, bedienen oder warten. Anwender müssen sich neben den Bestimmungen aller anwendbaren Vorschriften, Gesetze und Normen zusätzlich mit den Installations- und Verdrahtungsanweisungen vertraut machen.

Arbeiten im Rahmen der Installation, Anpassung, Inbetriebnahme, Verwendung, Montage, Demontage oder Instandhaltung dürfen nur durch ausreichend geschulte Mitarbeiter und in Übereinstimmung mit den anwendbaren Ausführungsvorschriften vorgenommen werden.

Wenn das Gerät in einer Weise verwendet wird, die vom Hersteller nicht vorgesehen ist, kann die Schutzfunktion beeinträchtigt sein.

ATTENTION : Lisez ce document et les documents listés dans la section Ressources complémentaires relatifs à l'installation, la configuration et le fonctionnement de cet équipement avant d'installer, configurer, utiliser ou entretenir ce produit. Les utilisateurs doivent se familiariser avec les instructions d'installation et de câblage en plus des exigences relatives aux codes, lois et normes en vigueur.

Les activités relatives à l'installation, le réglage, la mise en service, l'utilisation, l'assemblage, le démontage et l'entretien doivent être réalisées par des personnes formées selon le code de pratique en vigueur.

Si cet équipement est utilisé d'une façon qui n'a pas été définie par le fabricant, la protection fournie par l'équipement peut être compromise.

주의：본 제품 설치, 설정, 작동 또는 유지 보수하기 전에 본 문서를 포함하여 설치, 설정 및 작동에 관한 참고 자료 섹션의 문서들을 반드시 읽고 숙지하십시오. 사용자는 모든 관련 규정, 법규 및 표준에서 요구하는 사항에 대해 반드시 설치 및 배선 지침을 숙지해야 합니다.

설치, 조정, 가동, 사용, 조립, 분해, 유지보수 등 모든 작업은 관련 규정에서 정해진 교육을 받은 사용자를 통해서만 수행해야 합니다.

본 장비를 제조사가 명시하지 않은 방법으로 사용하면 장비의 보호 기능이 손상될 수 있습니다.

ATTENZIONE Prima di installare, configurare ed utilizzare il prodotto, o effettuare interventi di manutenzione su di esso, leggere il presente documento ed i documenti elencati nella sezione "Altre risorse", riguardanti l'installazione, la configurazione ed il funzionamento dell'apparecchiatura. Gli utenti devono leggere e comprendere le istruzioni di installazione e cablaggio, oltre ai requisiti previsti dalle leggi, codici e standard applicabili.

Le attività come installazione, regolazioni, utilizzo, assemblaggio, disassemblaggio e manutenzione devono essere svolte da personale adeguatamente addestrato, nel rispetto delle procedure previste.

Qualora l'apparecchio venga utilizzato con modalità diverse da quanto previsto dal produttore, la sua funzione di protezione potrebbe venire compromessa.

DIKKAT: Bu ürünün kurulumu, yapılandırılması, işletilmesi veya bakımı öncesinde bu dokümanı ve bu ekipmanın kurulumu, yapılandırılması ve işletimi ile ilgili ilave Kaynaklar bölümünde yer listelenmiş dokümanları okuyun. Kullanıcılar yürürlükteki tüm yönetmelikler, yasalar ve standartların gereksinimlerine ek olarak kurulum ve kablolarla talimatlarını da öğrenmek zorundadır.

Kurulum, ayarlama, hizmet alma, kullanma, parçaları birleştirme, parçaları sökme ve bakım gibi aktiviteler sadece uygun eğitimli almış kişiler tarafından yürürlükteki uygulama yönetmeliklerine uygun şekilde yapılabilir.

Bu ekipman üretici tarafından belirlenmiş amacın dışında kullanılırsa, ekipman tarafından sağlanan koruma bozulabilir.

注意事項：在安装、設定、操作或維護本產品前，請先閱讀此文件以及列於「其他資源」章節中有關安裝、設定與操作此設備的文件。使用者必須熟悉安裝和配線指示，並符合所有法規、法律和標準要求。

包括安裝、調整、交付使用、使用、組裝、拆卸和維護等動作都必須交由已經過適當訓練的人員進行，以符合適用的實作法規。

如果將設備用於非製造商指定的用途時，可能會造成設備所提供的保護功能受損。

POZOR: Než začnete instalovat, konfigurovat či provázovat tento výrobek nebo provádět jeho údržbu, přečtěte si tento dokument a dokumenty uvedené v části Dodatečné zdroje ohledně instalace, konfigurace a provozu tohoto zařízení. Uživatelé se musejí vedle požadavků všech relevantních vyhlásek, zákonů a norem nutně seznámit také s pokyny pro instalaci a elektrické zapojení.

Činnosti zahrnující instalaci, nastavení, uvedení do provozu, užívání, montáž, demontáž a údržbu musí vykonávat vhodné proškolený personál v souladu s příslušnými prováděcími předpisy.

Pokud se toto zařízení používá způsobem neodpovídajícím specifikaci výrobce, může být narušena ochrana, kterou toto zařízení poskytuje.

UWAGA: Przed instalacją, konfiguracją, użytkowaniem lub konserwacją tego produktu należy przeczytać niniejszy dokument oraz wszystkie dokumenty wymienione w sekcji Dodatkowe źródła omawiające instalację, konfigurację i procedury użytkowania tego urządzenia. Użytkownicy mają obowiązek zapoznać się z instrukcjami dotyczącymi instalacji oraz oprzewodowania, jak również z obowiązującymi kodeksami, prawem i normami.

Działania obejmujące instalację, regulację, przekazanie do użytkowania, użytkowanie, montaż, demontaż oraz konserwację muszą być wykonywane przez odpowiednio przeszkolony personel zgodnie z obowiązującym kodeksem postępowania.

Jeśli urządzenie jest użytkowane w sposób inny niż określony przez producenta, zabezpieczenie zapewniane przez urządzenie może zostać ograniczone.

OBBS! Läs detta dokument samt dokumentet, som står listat i avsnittet Övriga resurser, om installation, konfigurering och drift av denna utrustning innan du installerar, konfigurerar eller börjar använda eller utföra underhållsarbete på produkten. Användare måste bekanta sig med instruktioner för installation och kabeldragning, förutom krav enligt gällande koder, lagar och standarder.

Åtgärder som installation, justering, service, användning, montering, demontering och underhållsarbete måste utföras av personal med lämplig utbildning enligt lämpligt bruk.

Om denna utrustning används på ett sätt som inte anges av tillverkaren kan det hända att utrustningens skyddsanordningar försätts ur funktion.

LET OP: Lees dit document en de documenten die genoemd worden in de paragraaf Aanvullende informatie over de installatie, configuratie en bediening van deze apparatuur voordat u dit product installeert, configureert, bedient of onderhoudt. Gebruikers moeten zich vertrouwd maken met de installatie en de bedrijfsinstructies, naast de vereisten van alle toepasselijke regels, wetten en normen.

Activiteiten zoals het installeren, afstellen, in gebruik stellen, gebruiken, monteren, demonteren en het uitvoeren van onderhoud mogen uitsluitend worden uitgevoerd door hiervoor opgeleid personeel en in overeenstemming met de geldende praktijkregels.

Indien de apparatuur wordt gebruikt op een wijze die niet is gespecificeerd door de fabrikant, dan bestaat het gevaar dat de beveiliging van de apparatuur niet goed werkt.

Environment and Enclosure



ATTENTION: This equipment is intended for use in a Pollution Degree 2 industrial environment, in overvoltage Category II applications (as defined in EN/IEC 60664-1), at altitudes up to 2000 m (6562 ft) without derating.

This equipment is not intended for use in residential environments and may not provide adequate protection to radio communication services in such environments.

This equipment is supplied as open-type equipment for indoor use. It must be mounted within an enclosure that is suitably designed for those specific environmental conditions that will be present and appropriately designed to prevent personal injury resulting from accessibility to live parts. The enclosure must have suitable flame-retardant properties to prevent or minimize the spread of flame, complying with a flame spread rating of 5VA or be approved for the application if nonmetallic. The interior of the enclosure must be accessible only by the use of a tool. Subsequent sections of this publication may contain more information regarding specific enclosure type ratings that are required to comply with certain product safety certifications.

In addition to this publication, see the following:

- Industrial Automation Wiring and Grounding Guidelines, publication T770-4.1, for more installation requirements.
- NEMA Standard 250 and EN/IEC 60529, as applicable, for explanations of the degrees of protection provided by enclosures.

Prevent Electrostatic Discharge



ATTENTION: This equipment is sensitive to electrostatic discharge, which can cause internal damage and affect normal operation. Follow these guidelines when you handle this equipment:

- Touch a grounded object to discharge potential static.
- Wear an approved grounding wriststrap.
- Do not touch connectors or pins on component boards.
- Do not touch circuit components inside the equipment.
- Use a static-safe workstation, if available.
- Store the equipment in appropriate static-safe packaging when not in use.

Specific Conditions for Use



WARNING:

- The equipment can be used as an accessory in only a FLEXHA 5000 I/O system.
- Do not use the equipment outside a FLEXHA 5000 I/O system applications.
- When the equipment is used in a FLEXHA 5000 I/O system application, all system certifications apply.
- This equipment is not resistant to sunlight or other sources of UV radiation.
- This equipment shall be mounted in an UKEX/ATEX/IECEX/INMETRO Zone 2 certified enclosure with a minimum ingress protection rating of at least IP54 (in accordance with EN/IEC/ABNT NBR 60079-0) and used in an environment of not more than Pollution Degree 2 (as defined in EN/IEC 60664-1) when applied in Zone 2 environments. The enclosure must be accessible only by the use of a tool.
- This equipment shall be used within its specified ratings defined by Rockwell Automation.
- Transient protection shall be provided that is set at a level not exceeding 140% of the peak rated voltage value at the supply terminals to the equipment.
- The instructions in the user manual shall be observed.
- This equipment must be used only with UKEX/ATEX/IECEX/INMETRO certified Rockwell Automation backplanes.
- The equipment shall be installed in compliance with the enclosure, mounting, spacing and segregation requirements of the ultimate application.
- This equipment must be used with the following accessories.

Catalog Number	Description										
5015-A2AXT	Adapter Base Dual with Power Conditioner										
5015-BIMXT	Backplane Interface Module										
5015-BEKITXT	Bus Expansion Module, Power Cable and Communication Cable, used if extension of the backplane is needed. The 5015-BEKITXT consists of the following models:										
	<table border="1"> <thead> <tr> <th>Catalog Number</th> <th>Description</th> </tr> </thead> <tbody> <tr> <td>5015-BEBRXT</td> <td>Bank Expansion Base, Right</td> </tr> <tr> <td>5015-BEBLXT</td> <td>Bank Expansion Base, Left</td> </tr> <tr> <td>5015-BECPWRXT</td> <td>Backplane Power Extension Cable (length 2 m)</td> </tr> <tr> <td>5015-BECCOMXT</td> <td>Backplane Communication Extension Cable (length 2 m)</td> </tr> </tbody> </table>	Catalog Number	Description	5015-BEBRXT	Bank Expansion Base, Right	5015-BEBLXT	Bank Expansion Base, Left	5015-BECPWRXT	Backplane Power Extension Cable (length 2 m)	5015-BECCOMXT	Backplane Communication Extension Cable (length 2 m)
	Catalog Number	Description									
	5015-BEBRXT	Bank Expansion Base, Right									
	5015-BEBLXT	Bank Expansion Base, Left									
5015-BECPWRXT	Backplane Power Extension Cable (length 2 m)										
5015-BECCOMXT	Backplane Communication Extension Cable (length 2 m)										
5015-BPGNDXT	Back Plate GND Lug (part of backplate)										

- This equipment must be used with one of the following accessories.

Catalog Number	Description
5015-MP300XT	Mounting Plate 300 mm
5015-MP700XT	Mounting Plate 700 mm
5015-MP900XT	Mounting Plate 900 mm
5015-MP1250XT	Mounting Plate 1250 mm



ATTENTION:

- In case of malfunction or damage, no attempts at repair should be made. The module should be returned to the manufacturer for repair. Do not dismantle the module.
- Use only a soft dry anti-static cloth to wipe down equipment. Do not use any cleaning agents.

Install the Bank Expansion Bases

To install the Bank Expansion Base, Left, complete the following steps.

IMPORTANT Remember, this example shows how to connect a Bank Expansion Base, Left to an I/O Base in an Adapter Bank. You can connect the Bank Expansion Base, Left to an Adapter Base and the same steps apply.

1. Install the Adapter Base and I/O Base(s), if necessary, on the Adapter Bank.
 2. If an end cap is installed on the base to which you are connecting the Bank Expansion Base, Left, remove it.
 3. Seat the bottom of the Bank Expansion Base, Left, in the hooked portion of the mounting plate and against the last base in the Bank. The last base can be the Adapter Base or an I/O Base.
 4. Push the top of the Bank Expansion Base, Left, toward the mounting plate.

When the Bank Expansion Base, Left, is moving toward the I/O Base, a tab on the left side of the Bank Expansion Base, Left, enters a slot on the right side of the I/O Base.

As the rotation toward the mounting plate continues, a rectangular opening on the left side of the Bank Expansion Base, Left, engages a tab on the right side of the I/O Base.
 5. Continue to push the Bank Expansion Base, Left, toward the top of the mounting plate until it snaps into place.

When the Bank Expansion Base, Left, is fully installed, it appear as follows.
 6. Use a #2 Phillips screwdriver to turn the ST4.8 metric fastener to secure the base to the mounting plate.


The torque is 2 +/-0.11 Nm (18 +/-1 in-lb).
 7. On another mounting plate, seat the bottom of the Bank Expansion Base, Right, in the hooked portion of the mounting plate.
 8. Push the top of the Bank Expansion Base, Right, toward the mounting plate until it snaps into place.
 9. Use a #2 Phillips screwdriver to turn the ST4.8 metric fastener to secure the base to the mounting plate.

The torque is 2 +/-0.11 Nm (18 +/-1 in-lb).
 10. Seat the bottom of the I/O Base in the hooked portion of the mounting plate.
 11. Push the top of the I/O Base toward the mounting plate.

When the I/O Base is moving toward the mounting plate, a tab on the left side of the I/O Base enters an opening on the right side of the Bank Expansion Base, Right.

As the rotation toward the mounting plate continues, a rectangular opening on the left side of the I/O Base engages a tab on the right side of the Bank Expansion Base, Right.
 12. Continue to push the I/O Base toward the top of the mounting plate until it snaps into place.

When the I/O Base is fully installed next to the Bank Expansion Base, Right, it appear as follows.
 13. Use a #2 Phillips screwdriver to turn the ST4.8 metric fastener to secure the base to the mounting plate.

The torque is 2 +/-0.11 Nm (18 +/-1 in-lb).
 14. If you are using multiple I/O Bases on the I/O Bank, repeat the tasks that are described in [step 10](#) on [page 4](#) through [step 13](#) on [page 4](#) to install the next I/O Base.
 15. Complete one of the following tasks.
 - a. If you are not using multiple I/O Banks, install an end cap and skip to [Connect the Adapter and I/O Banks Via Extension Cables on page 4](#).
 - b. If you are using multiple I/O Banks, proceed to the next step.
-  In [step 10](#), the I/O Base connects to a Bank Expansion Base, Right. Additional I/O Bases on the bank connect to I/O Bases.
16. If an end cap is installed, pull it off the last I/O Base on the first I/O Bank.
 17. Seat the bottom of the Bank Expansion Base, Left, in the hooked portion of the mounting plate.
 18. Push the top of the Bank Expansion Base, Left, toward the mounting plate.

When the Bank Expansion Base, Left, is moving toward the I/O Base, a tab on the left side of the Bank Expansion Base, Left, enters an opening on the right side of the I/O Base.

As the rotation toward the mounting plate continues, a rectangular opening on the left side of the Bank Expansion Base, Left, engages a tab on the right side of the I/O Base.
 19. Continue to push the Bank Expansion Base, Left, toward the top of the mounting plate until it snaps into place.

When the Bank Expansion Base, Left, is fully installed, the locations that connect the Bank Expansion Base, Left, to the I/O Base appear as follows.
 20. Use a #2 Phillips screwdriver to turn the ST4.8 metric fastener to secure the base to the mounting plate.

The torque is 2 +/-0.11 Nm (18 +/-1 in-lb).
 21. To install the second I/O bank, repeat [step 7](#) on [page 4](#) through [step 14](#) on [page 4](#).



Connect the Adapter and I/O Banks Via Extension Cables

After you install the I/O Bases across multiple banks, you must use Backplane Communication Extension cables and Backplane Power Extension cables between the Backplane Extension Modules to connect the banks.

- IMPORTANT**
- When you use Backplane Communication and Power Extension cables, you must consider factors, such as applying proper bend radius, applying strain relief, and separating cables from high-voltage cables.
 - Make sure that you connect cables to corresponding ports on the other Bank Expansion Module. For example, if you connect a cable to the bottom port on the Bank Expansion Module, left, you must connect the other end of that cable to the bottom port on the Bank Expansion Module, right.
- For more details on all factors that you must consider before connecting banks, see the FLEXHA 5000 I/O System Installation Instructions, publication [5015-IN001](#).

Connect the Backplane Communication Extension Communication Cables

To connect the Backplane Communication Extension cables, complete the following steps.


1. Remove the dust cover from the Bank Expansion Base, Left.
2. Plug the end of a Backplane Communication Extension cable that is **marked with an A** into port **Data A** on the Bank Expansion Base, Left, that is installed on the Adapter bank.
 -  Backplane Communication Extension cables are polarized and marked with an A on one end and a B on the other. You can only connect specific ends of the cables to specific ports on a Bank Expansion Base, Left, and the other ends of the cables to specific ports on the Bank Expansion Base, Right.
 - The A on the cable does not always correspond to Data A ports on the Bank Expansion Base. For example, the top data port on both Bank Expansion Bases is labeled Data A. So on the top, the Data A end of the cable plugs into a Data A port. The other end of that cable, marked B, plugs in a Data A port.
 - Make sure that you hold the connector housing, and not the cable, when you push the cable into the port.
3. Remove the dust cover from the Bank Expansion Base, Right.
4. Plug the end of the Backplane Communication Extension cable that is **marked with a B** into port **Data A** on the Bank Expansion Base, Right, that is installed on the first I/O bank.
 -  Make sure that you hold the connector housing, and not the cable, when you push the cable into the port.
5. Repeat [step 2](#) through [step 4](#) to connect the Backplane Communication Extension cable from port Data B on the Bank Expansion Base, Left, to port Data B on the Bank Expansion Base, Right.
6. If you are using two I/O Banks, repeat [step 1](#) on [page 4](#) through [step 5](#) on [page 4](#) to connect the Backplane Communication Extension cables between the first I/O bank and the second I/O bank.

Connect the Backplane Power Extension Communication Cables

To connect the Backplane Power Extension cables, complete the following steps.

1. Remove the caps from the cable receptacles on the Bank Expansion Base.
2. Plug one end of a Backplane Power Extension cable that has male connectors a power port on the Bank Expansion Base, Left, that is installed on the Adapter Bank, and begin to tighten the cable in place.

Power ports on the Bank Expansion Base, Left, have female connectors.

 -  Backplane Power Extension cables are polarized. You can only connect specific ends of the cables to specific ports on a Bank Expansion Base, Left, and the other ends of the cables to specific ports on the Bank Expansion Base, Right.
 - Make sure that you hold the connector housing, and not the cable, when you push the cable into the port.
3. Use a torque wrench to finish tightening the cable in place.

The recommended torque is 0.6 Nm (5.3 in-lb).
4. Plug the other end of the Backplane Power Extension cable to a power port on the Bank Expansion Base, Right, that is installed on the first I/O Bank, and begin to tighten the cable in place.

The other end of the Backplane Power Extension cable uses female connectors and power ports on the Bank Expansion Base, Right, have male connectors.

We recommend that you connect the Backplane Power Extension cables to the same port positions. That is, if you connect a Backplane Power Extension cable to the top power port on a Bank Expansion Base, Left, connect the other end of the cable to the top power port on the Bank Expansion Base, Right.
5. Use a specialty torque wrench to finish tightening the cable in place.

The recommended torque is 0.6 Nm (5.3 in-lb).
6. Repeat [step 2](#) through [step 5](#) to connect a Backplane Power Extension cable from port Power B on the Bank Expansion Base, Left to port Power B port on the Bank Expansion Base, Right.
7. If you are using two I/O Banks, repeat [step 1](#) on [page 4](#) through [step 6](#) on [page 4](#) to connect the Backplane Communication Extension and Backplane Power Extension cables between the first I/O bank and the second I/O bank.

Specifications

For a list of all specifications, see the FLEXHA 5000 I/O System Specifications Technical Data, publication [5015-TD001](#).

5015-BEBLXT, 5015-BEBRXT Bank Expansion Bases, Left and Right, Specifications

Attribute	Value
Temperature, operating IEC 60068-2-14 (Test Na and Nb, Non Operating and Operating Thermal Shock)	$-40\text{ }^{\circ}\text{C} \leq T_a \leq +70\text{ }^{\circ}\text{C}$ ($-40\text{ }^{\circ}\text{F} \leq T_a \leq +158\text{ }^{\circ}\text{F}$)
Temperature, surrounding air, max	70 °C (158 °F) - If the Bank Expansion Base is installed in an Adapter Base or an I/O Base that is mounted horizontally. 60 °C (140 °F) - If the Bank Expansion Base is installed in an I/O Base that is mounted vertically.
Wiring category ⁽¹⁾	3 - signal ports (Data) 3 - power ports (Power)

(1) Use this Conductor Category information for planning conductor routing as described in the appropriate System Level Installation Manual. Also refer to Industrial Automation Wiring and Grounding Guidelines, publication [1770-4.3](#), for more installation information.

Additional Resources

These documents contain additional information concerning related products from Rockwell Automation.

Resource	Description
FLEXHA 5000 I/O System Installation Instructions, publication 5015-INO01	Describes how to install a FLEXHA 5000 I/O system.
FLEXHA 5000 I/O System User Manual, publication 5015-UM001	Describes how to configure, maintain, and troubleshoot a FLEXHA 5000 I/O system.
FLEXHA 5000 I/O System Specifications Technical Data, publication 5015-TD001	Provides specifications and wiring diagrams for FLEXHA 5000 I/O modules, EtherNet/IP™ adapter, and other system components.
Industrial Components Preventive Maintenance, Enclosures, and Contact Ratings Specifications, publication IC-TD002	Provides a quick reference tool for Allen-Bradley® industrial automation controls and assemblies.
Industrial Automation Wiring and Grounding Guidelines, publication 1770-4.3	Provides general guidelines for installing a Rockwell Automation industrial system.
Safety Guidelines for the Application, Installation, and Maintenance of Solid-state Control, publication SGI-1.1	Designed to harmonize with NEMA Standards Publication No. ICS 1.1-1987 and provides general guidelines for the application, installation, and maintenance of solid-state control in the form of individual devices or packaged assemblies incorporating solid-state components.
Product Certifications website, rok.auto/certifications	Provides declarations of conformity, certificates, and other certification details.

You can view or download publications at [rok.auto/literature](#).

Notes:

Notes:

Rockwell Automation Support

Use these resources to access support information.

Technical Support Center	Find help with how-to videos, FAQs, chat, user forums, and product notification updates.	rok.auto/support
Knowledgebase	Access Knowledgebase articles.	rok.auto/knowledgebase
Local Technical Support Phone Numbers	Locate the telephone number for your country.	rok.auto/phonesupport
Literature Library	Find installation instructions, manuals, brochures, and technical data publications.	rok.auto/literature
Product Compatibility and Download Center (PCDC)	Download firmware, associated files (such as AOP, EDS, and DTM), and access product release notes.	rok.auto/pcdc

Documentation Feedback

Your comments help us serve your documentation needs better. If you have any suggestions on how to improve our content, complete the form at rok.auto/docfeedback.





Waste Electrical and Electronic Equipment (WEEE)



At the end of life, this equipment should be collected separately from any unsorted municipal waste.

Rockwell Automation maintains current product environmental compliance information on its website at rok.auto/pec.

Rockwell Otomasyon Ticaret A.Ş. Kar Plaza İş Merkezi E Blok Kat:6 34752, İçerenköy, İstanbul, Tel: +90 (216) 5698400 EEE Yönetmeliğine Uygundur

Connect with us.    

rockwellautomation.com — expanding **human possibility**[®]

AMERICAS: Rockwell Automation, 1201 South Second Street, Milwaukee, WI 53204-2496 USA, Tel: (1) 414.382.2000, Fax: (1) 414.382.4444

EUROPE/MIDDLE EAST/AFRICA: Rockwell Automation NV, Pegasus Park, De Kleetlaan 12a, 1831 Diegem, Belgium, Tel: (32) 2 663 0600, Fax: (32) 2 663 0640

ASIA PACIFIC: Rockwell Automation, Level 14, Core F, Cyberport 3, 100 Cyberport Road, Hong Kong, Tel: (852) 2887 4788, Fax: (852) 2508 1846

UNITED KINGDOM: Rockwell Automation Ltd. Pitfield, Kiln Farm Milton Keynes, MK11 3DR, United Kingdom, Tel: (44)(1908) 838-800, Fax: (44)(1908) 261-917

Allen-Bradley, expanding human possibility, FLEXHA 5000, and Rockwell Automation are trademarks of Rockwell Automation, Inc.

EtherNet/IP is a trademark of ODVA, Inc.

Trademarks not belonging to Rockwell Automation are property of their respective companies.

Publication 5015-PC003A-EN-P - December 2022

Copyright © 2022 Rockwell Automation, Inc. All rights reserved. Printed in the U.S.A.

PN-676604