

Next Generation Industrial UPS

Features and Benefits

The 1609 family of Industrial Uninterruptible Power Supplies is designed for industrial applications – with features required for remote control and operation inside of industrial control panels.

DIN-rail/panel/floor mount

- Flexibility to meet most installation scenarios, included control panels typically used in production environments.

Hard-wired input and output

- Electrical codes typically do not allow plug-in connections within a control panel.

Integrated remote on/off and Dry I/O contacts

- Meet code requirements to allow proper shutdown of the UPS when control panel is open and closed and provide for remote monitoring and control of UPS.

USB communications

- Provides remote monitoring and configuration through included software

True sine wave AC output

- Compatible with the widest range of equipment.

Expandable battery capacity

- Additional batteries can be added to the UPS to extend run-time or accommodate additional equipment. (1609-D Only)

EtherNet/IP communications

- Allows the ability to communicate with and integrate to Rockwell Automation Integrated Architecture. 1609-D Only)



Faster Recovery From Power Failures


An industrial uninterruptible power supply (UPS) can enable your production process to recover quickly from a line power interruption, saving you lost production time and work in process. Sometimes users think that because there isn't a battery large enough to keep the process itself going, a UPS won't make any difference. What a UPS can do effectively, is to keep the control system, networks and sensors powered, so when power returns, the control system knows where everything is and can start up without having to completely reset and clear the work in process.

The 1609 is uniquely designed for the industrial market to provide back-up AC power to the control cabinet. The 1609 will provide back-up power to bridge dips, sags, or brief losses of power. If necessary, the 1609 will facilitate a safe shut-down of your industrial PC, PLC, data logging HMI, or any other critical device in the control scheme. Without a 1609 in place, the customer is faced with nuisance power dips, extended down-time, and potential machine damage; all of which can result in significant and costly challenges

The newer technologies of industrial controls are much more sensitive to power fluctuations, the need for clean consistent reliable power continues to grow as industrial automation and process control continues to migrate more towards more sensitive electronic controls and extensive networking. Industrial UPS products are about increasing system reliability and minimizing down time due to power disruptions and product failures in the control system.

LISTEN.
THINK.
SOLVE.

	Panel Mount	Integrated Dry I/O Contacts	Remote On/Off	Replaceable Surge Protection	EtherNet/IP	USB	AVR	Expandable Battery
1609-B	•	•	•	•		•		
1609-D	•	•	•	•	•	•	•	•



Input		VA	1609-B	1609-D	
Capacity		600	600VA (390W)	600VA (390W)	
		1000	1000VA (390W)	1000VA (650W)	
		1500	N/A	1500VA (980W)	
Voltage Range 120VAC/230VAC		90...145V/184...264			
Current	1609-B	Input Voltage	600VA	1000VA	1500VA
		120V	5.4A	8.9A	N/A
	1609-D	230V	2.8A	4.7A	N/A
		120V	5.5A	8.8A	13A
	230V	3.3A	4.7A	7.1A	
Capacity Frequency		50/60Hz +/- 3Hz			
PFC		None (Load power factor is reflected in the input line)			

Output		VA	1609-B	1609-D
Capacity		600	600VA (390W)	600VA (390W)
		1000	1000VA (390W)	1000VA (650W)
		1500	N/A	1500VA (980W)

Online		120VAC	230VAC
Output Range	1609-B	96...138	184...265
	1609-D	108...132	207...253
Transfer Point Accuracy		+/- 3%	

On Battery		120V/230V
V Nom.		120V/230V
Frequency		50/60Hz±0.5Hz (Factory Default: 60Hz±0.5Hz)
THD		≤10% (Full Linear Load)
Run Time		Battery dependent. 1609-B600E & B1000E limited to 12 minutes.

Short Circuit Protection	
Crest Factor	2.2:1

Efficiency	
On Battery	75% (Typical with resistive load)
On Line	86% (Typical with resistive load excluding AVR mode)

Protection	
Surge	380 Joules (Total Performance Rated With 10*1000ms Pulse)
Overload	>110-130% Shutdown after 10 Seconds >130% Shutdown immediately
Output Short On Line	Premises branch circuit over-current protection
Output Short On Battery	Shutdown
Thermal Protection	UPS inside temperature 60 degree C
Bypass	N/A

Regulatory	
Safety	UL1778, CSA C22.2 No. 107.3-05, EN/IEC62040-1
EMC	FCC & CE (Class A)
Markings	UL, cUL, FCC, CE

Battery Pack	
Run Time	≥5 Minutes (at 25 degree C, full R load)
Type	Sealed Lead Acid Battery
Rated Capacity	0-40°C: B.B. BP5-12 0-50°C: B.B. HRL5.5-12 12V/5.5Ah
Charger	Current limited, constant voltage float charger
Recharge Time	Less than 8 hours to 90% capacity after discharged with full load
Lifetime	2~3 years @ 25 degree C ambient

Environmental		
Operating Temperature – Standard Battery	0°C~40°C (32°F~104°F) 0°C~50°C (32°F~122°F)	
Operating Temperature – Hi Temperature Battery	0°C~50°C (32°F~122°F)	
Storage Temperature	- 15...45°C (5°F...113°F)	
Altitude	Operating 0 ... 6600 feet (0 to 2000 meters)	
Humidity	Operating/Storage 5~95 % RH (Non-condensing)	
Heat Output	On Line, Full load:	217 BTU per hour
	On Line, Full load, Charging:	296 BTU per hour
	On Battery: Full Load:	1331 BTU per hour
Audible Noise	50 dBA at front side one meter	

Allen-Bradley, LISTEN. THINK. SOLVE. and Rockwell Software are trademarks of Rockwell Automation, Inc. Trademarks not belonging to Rockwell Automation are property of their respective companies.

*1500VA only offered in 1609-D family

www.rockwellautomation.com

Power, Control and Information Solutions Headquarters

Americas: Rockwell Automation, 1201 South Second Street, Milwaukee, WI 53204-2496 USA, Tel: (1) 414.382.2000, Fax: (1) 414.382.4444

Europe/Middle East/Africa: Rockwell Automation NV, Pegasus Park, De Kleetlaan 12a, 1831 Diegem, Belgium, Tel: (32) 2 663 0600, Fax: (32) 2 663 0640

Asia Pacific: Rockwell Automation, Level 14, Core F, Cyberport 3, 100 Cyberport Road, Hong Kong, Tel: (852) 2887 4788, Fax: (852) 2508 1846