

Bulletin 9300-ENA Network Address Translation (NAT) Device

More flexible network configuration at a lower cost

Benefits

- Gives flexibility to control systems by allowing identical machines to be placed on Ethernet networks
- Offers the ability to apply consistent configurations to control systems on a network
- Provides original equipment manufacturers the ability to offer remote support through VPN connections

Features

- **Flexibility**
Make network configuration changes easily for all of your control systems to meet your exact specifications
- **Precision**
Configure each machine with identical network settings repeatedly, so they can communicate on the same network
- **Value**
The 9300-ENA discovery feature lets you view all devices on your network and configure your line to receive remote support troubleshooting and monitoring, cutting down on costly on-site service calls



Looking to increase the flexibility in your small control system? The Allen-Bradley® 9300-ENA can help your plant configure multiple machines on the same line to have identical network settings, allowing easy remote support by VPN connection.

The 9300-ENA will adapt your machinery to specific network configurations without complicated, costly and time-consuming changes, giving identical control systems the ability to communicate on an Ethernet network without reconfiguring its settings.

And it's fast. The 9300-ENA supports 1 Gbps Ethernet speed for excellent network performance.

9300-ENA NAT Device Specifications


Attribute	Specifications
Environmental Operating Temperature Storage Temperature Weight	0...60 °C (32...152 °F) -20...70 °C (-4...158 °F) 1.5 lb
Compliance	UL/CUL/ATEX Certified, CE, UL Class 1 DIV 2 Hazardous
Power Requirements	12 to 48VDC (240ma typical, 300ma Max)
Network Connections	3 RJ-45 10/100/1000 Mbps full/half duplex jacks
NAT Devices Supported	128 devices

Ordering





To order, use bulletin number 9300-ENA.

For More Information

Contact your local authorized Allen-Bradley distributor, Rockwell Automation sales office or visit <https://ab.rockwellautomation.com/Networks-and-Communications/Network-Address-Translation-Device>



3216-M

Connect with us.    

rockwellautomation.com

expanding human possibility™

AMERICAS: Rockwell Automation, 1201 South Second Street, Milwaukee, WI 53204-2496 USA, Tel: (1) 414.382.2000, Fax: (1) 414.382.4444
 EUROPE/MIDDLE EAST/AFRICA: Rockwell Automation NV, Pegasus Park, De Kleetlaan 12a, 1831 Diegem, Belgium, Tel: (32) 2 663 0600, Fax: (32) 2 663 0640
 ASIA PACIFIC: Rockwell Automation, Level 14, Core F, Cyberport 3, 100 Cyberport Road, Hong Kong, Tel: (852) 2887 4788, Fax: (852) 2508 1846

Allen-Bradley, Rockwell Automation and Rockwell Software are trademarks of Rockwell Automation, Inc.
 Trademarks not belonging to Rockwell Automation are property of their respective companies.

Publication GMSP-PP001C-EN-P - August 2019 | Supersedes Publication GMSP-PP001B-EN-P - April 2014
 Copyright © 2019 Rockwell Automation, Inc. All Rights Reserved. Printed in USA.