**Original Instructions** 



# **1442 Eddy Current Probe Systems Specifications**

Catalog Numbers 1442-PS series, 1442-PR series, 1442-EC series, 1442-DR series

Торіс	
Summary of Changes	2
Non-contact Pick-up Probe System	3
Wiring Guidelines	3
Match System Components by Color	4
1442 Series Probe System Specifications	
1442 Series Catalog Numbers	
Additional Resources	

The 1442 series of eddy current probe systems serve applications with measurement ranges from 0.1...29 mm (4...1142 mils). 1442 series probe systems fully satisfy the requirements of API 670 and are suitable for any type of dynamic or static displacement measurement, including vibration, speed/acceleration, rotor/position, and differential expansion measurements.




## **Summary of Changes**

This publication contains the following new or updated information. This list includes substantive updates only and is not intended to reflect all changes.

Торіс	Page
Updated CCC Ex Certifications information	6

## **Non-contact Pick-up Probe System**

A non-contact pick-up probe system is composed of three components.



Component	Description
Non-contact pick-up probe	The non-contact pick-up probe is an encapsulated wire configuration that reads the relative position of the equipment by introducing eddy currents into the target material and measuring the change in the current as the target surface moves. The energy loss into the target increases or decreases as the target moves nearer to or farther away from the probe. The change in energy loss is detected as a change in the modulated signal. This change provides a voltage proportional to the gap between the probe tip and the target. This signal is fed to the monitoring system, providing a continuous and very accurate measure of the relative distance to the target surface. The tip diameter characterizes the probe. In general, the wider the tip, the greater the range that the probe can sense. Choose other characteristics, such as the body length and the thread size, based on the application.
Extension cable	The extension cable provides flexibility for placement of the probe by allowing extended lengths between the driver and the non-contact pick-up. A variety of Teflon-insulated and Armor-coaxial extension cables adapt the probe system to most installations. The extension cables are electrically matched to the selected probe system.
Driver	The driver systems are case-isolated and can be DIN rail or panel mounted. The stainless-steel probe drivers provide the radio frequency that powers the probe system. The driver is the primary component responsible for signal conditioning, providing accurate linearity over the operating range of the system.

## **Wiring Guidelines**

When wiring the probe driver to a monitor, consider the following recommendations:

- Use a good quality instrumentation cable with three-conductor stranded wire and shield. Also consider the following:
  - Use wire rated with a maximum capacitance of 60 pF/ft (197 pF/m) and inductance of 0.3 µH/ft (1 µH/m).
  - Use wire with insulation suitable for the environment and with adequate tensile strength and flexibility for the application.
  - Use wire with a foil shield for use in environments where radio frequency interference (RFI) can be present.
  - Use wire with a braid shield for environments where electromagnetic interference (EMI) can be present.
  - Use 0.75...1.25 mm<sup>2</sup> (18...16 AWG).
- Make sure that the wire is isolated from power cables and any other wiring that can be transmitting high-voltage power or control signals.
- Isolate any cable transmitting pulse-type vibration signals, such as a phase marker or speed pulse, from displacement and vibration signals.
- Run wire within conduit and cable trays and as per any local electrical codes.
- Do not exceed 500 m (1640 ft). However, limiting the length to 300 m (984 ft) guarantees that vibration signals in the 0...10 kHz frequency range are transmitted with minimal attenuation. When longer lengths are needed, the capacitance of the cable and the desired frequency response of the system must be considered.
- In most cases, make sure that the cable shield is grounded at only one point, generally at the monitor.

## **Match System Components by Color**

The 1442 probe systems use color-coded bands to match probes and extension cables with the appropriate driver. The color-coded bands provide a system to identify the length of the extension cable and the length of the probe. By doing so, the total system length, 5 m or 9 m (16 ft or 29 ft), can be matched to the appropriate driver. When a system is properly sized, the color bands on either side of the connectors between the probe, extension cable, and driver match.

#### 1442 Series Color Bands

Probe Extension Cable		Driver				
Cable Length	Color Band	Length	Probe End Color Band	<b>Driver End Color Band</b>	System Cable Length	Color Band
0.5 m (1.64 ft)	Yellow	4.0 m (13.12 ft)	Black	Blue	5.0 m (16.40 ft)	Blue
1.0 m (3.28 ft)	Black	4.5 m (14.76 ft)	Yellow	Blue	9.0 m (29.53 ft)	Red
		8.0 m (26.25 ft)	Black	Red		
		8.5 (27.89 ft)	Yellow	Red		

# **1442 Series Probe System Specifications**

#### **Individual Technical Specifications**

Attribute	5 mm (0.20 in.)	8 mm (0.31 in.)	11 mm (0.43 in.)	18 mm (0.71 in.)	25 mm (1 in.)	50 mm (1.97 in.)
Applications (typical)	typical) Vibration, speed, or thrust			Differential expansion		
Linear range, approx <sup>(1)</sup>	2 mm (80 mils)		4.5 mm (180 mils)	6.0 mm (246 mils)	13.5 mm (532 mils)	26 mm (1024 mils)
Linear range from probe tip, approx <sup>(1)</sup>	0.252.25 mm (9.888.6 mils)		0.55.0 mm (20200 mils)	0.56.5 mm (20256 mils)	316.5 mm (118650 mils)	329 mm (1181142 mils)
Sensitivity <sup>(1)</sup>	7.87 V/mm (200 mV/mil)		3.94 V/mm (100 mV/mil)	2.5 V/mm (63.5 mV/mil)	0.8 V/mm (20.3 mV/mil)	0.4 V/mm (10.15 mV/mil)
Frequency response	DC to 10 kHz (-3 dB)		DC to 10 kHz (-3 dB)		DC to 200 Hz (-3 dB)	
5 m (16 ft) System Len	gth					
Scale factor error <sup>(1) (2)</sup>	Within 7.87 V/mm ±5% Within ±10%		Within 3.94 V/mm ±10%	_		
Linearity <sup>(2)</sup>	Within ±25 µm (±1 mil) for a straight line of 7.87 V/mm		Within ±100 µm for a straight line of 3.94 V/mm	Within ±90 µm for a straight line of 2.5 V/mm	Within ±270 µm for a straight line of 0.8 V/ mm	Within ±400 µm for a straight line of 0.4 V/ mm
9 m (29 ft) System Len	ngth					•
Scale factor error <sup>(1) (2)</sup>	Within ±6.5% of 7.87 V/mm (200 mV/mil)		Within ±10% of 3.94 V/mm (100 mV/ mil)	-		
Operating temperature	e characteristics <sup>(3)</sup>					
Probe <sup>(4)</sup>	< ±3% of F.S.					
Extension cable <sup>(4)</sup>	< ±4% of F.S. < ±3%		< ±3% of F.S.			
Driver <sup>(4)</sup>	< ±3% of F.S.					
Apply with gap	2 mm (0.08 in.)		4 mm (0.16 in.)	5 mm (0.20 in.)	14 mm (0.55 in.)	25 mm (0.98 in.)

<sup>(1)</sup> Applies at 25 °C (77 °F) with -24V DC power supply, load resistance 10 kΩ, and AISI 4140 (JIS SCM440) steel flat surface target (thickness ≥ 5 mm).

<sup>(2)</sup> Includes interchangeability errors.

<sup>(3)</sup> Applies when target is AISI 4140 (JIS SCM440) steel, flat, and with a thickness of >= 5 mm (0.2 in.).

<sup>(4)</sup> Applies at temperatures from 0...80 °C (176 °F) and is 0% F.S. at standard 20 °C (68 °F).

## **Common Technical Specifications**

Attribute	1442 Series Probe Systems
Standard calibration	AISI 4140 (JIS SCM440) steel flat surface
Maximum output voltage, approx <sup>(1)</sup>	-23V DC
Probe/sensor abnormal output voltage, approx <sup>(1)</sup>	-0.6V DC (probe/sensor OPEN or SHORT)
Current consumption (10 $k\Omega$ load), max	-15 mA
Output noise, approx <sup>(1)</sup>	20 mV peak-to-peak + power supply noise
Cable diameter, approx	2.7 mm or 3.6 mm (0.11 in. or 0.14 in.)
Connector diameter, approx	7.1 mm (0.28 in.)
Connector diameter (armored), approx	5.8 mm (0.23 in.)
System cable length	5 m or 9 m (16.40 ft or 29.53 ft) nominal
Probe integral cable variance	+30% / -0%
Extension cable variance	+20% / -0%
Power supply	-24V DC
Driver insulation resistance	Between terminals and mounting plate: $\geq$ 100 M $\Omega$ @ 500V DC
Terminal block	Spring lock terminal
Isolation voltage (driver)	50V (continuous), Basic Insulation Type, terminals to mounting plate Type tested at 500V AC for 60 s
Wiring category <sup>(2)</sup>	2 - on signal ports
Wire size (driver)	0.751.25 mm <sup>2</sup> (1816 AWG) shielded stranded-copper wire rated at 90 °C (194 °F), or greater, 1.2 mm (3/64 in.) insulation max
Driver mass, approx	200 g (7.0 oz.)

<sup>(1)</sup> Applies at 25 °C (77 °F) with -24V DC power supply, load resistance 10 kΩ, and AISI 4140 (JIS SCM440) steel flat surface target (thickness ≥ 5 mm).

## **Environmental Specifications**

Attribute	1442-Px Probe	1442-DRx Driver	1442-ECx Extension Cable	
Temperature, operating (Hazardous Area)	-40+80°C (-40+176 °F)			
Temperature, operating IEC 60068-2-1 (Test Ad, Operating Cold), IEC 60068-2-2 (Test Bd, Operating Dry Heat), IEC 60068-2-14 (Test Nb, Operating Thermal Shock)	-40+80 °C (-40+176 °F)	-40+177 °C (-40+350 °F) Connector: -40+80 °C (-40+176 °F)		
Relative humidity IEC 60068-2-30 (Test Db, Unpackaged Damp Heat)	3095% RH (noncondensing, nonsubmerged) Probe/sensor body: 100% RH			
Vibration IEC 60068-2-6 (Test Fc, Operating)	1 g @ 10150 Hz			
Emissions <sup>(1)</sup> CISPR11 (IEC 61000-6-4)	Class A	Class A	-	
ESD immunity <sup>(1) (2)</sup> IEC 61000-4-2	6 kV contact discharges 8 kV air discharges	6 kV contact discharges 8 kV air discharges	-	
Radiated RF immunity <sup>(1) (2)</sup> IEC 61000-4-3	10V/m with 1 kHz sine-wave 80% AM from 802000 MHz 3V/m with 1 kHz sine-wave 80% AM from 14002000 MHz 1V/m with 1 kHz sine-wave 80% AM from 20002700 MHz	10V/m with 1 kHz sine-wave 80% AM from 802000 MHz 3V/m with 1 kHz sine-wave 80% AM from 14002000 MHz 1V/m with 1 kHz sine-wave 80% AM from 20002700 MHz	_	
EFT/B immunity <sup>(1) (2)</sup> IEC 61000-4-4	±1 kV at 5 kHz on shielded signal ports	±1 kV at 5 kHz on shielded signal ports	-	

<sup>(2)</sup> Use this Conductor Category information for planning conductor routing. Refer to Industrial Automation Wiring and Grounding Guidelines, publication 1770-4.1.

### **Environmental Specifications (Continued)**

Attribute	1442-Px Probe	1442-DRx Driver	1442-ECx Extension Cable
Surge transient immunity <sup>(1)</sup> (2) IEC 61000-4-5	±1 kV line-earth (CM) on shielded signal ports	±1 kV line-earth (CM) on shielded signal ports	-
Conducted RF immunity <sup>(1) (2)</sup> IEC 61000-4-6	10V rms with 1 kHz sine-wave 80% AM from 150 kHz80 MHz	10V rms with 1 kHz sine-wave 80% AM from 150 kHz80 MHz	-
Magnetic field immunity IEC 61000-4-8	30 A/m long duration at 50 Hz		-
Enclosure type rating	None (open-style)		
Temperature code	T4		

<sup>(1)</sup> Two ferrite cores (TDK ZCAAT3035-1330 or equivalent) must be installed between 1442-DR-11xx and 1442-DR-58xx drivers and the 1442-PS-11xx, 1442-PR-08xx, 1442-PS-05xx, and 1442-PS-08xx probes.

#### Certifications

Certification <sup>(1)</sup>	1442 Series Probe Systems
cCSAus	CSA Certified Process Control Equipment for Class I, Divisions 1 and 2, Groups A,B,C,D Hazardous Locations, certified for US and Canada. See CSA File 216284.
RCM	Australian Radiocommunications Act, compliant with:  • EN 61326-1; Meas./Control/Lab., Industrial Requirements
CE	EU EMC Directive (2014/30/EU), compliant with:  • EN 61326-1; Meas./Control/Lab., Industrial Requirements  • EN 61326-2-3; Transducers  • EN 61000-6-2; Industrial Immunity  • EN 61000-6-4; Industrial Emissions  EU ATEX Directive (2014/34/EU), compliant with:  • EN 60079-0; Explosive Atmospheres, General Requirements  • EN 60079-11; Explosive Atmospheres, Protection "i"  • II 1 G Ex ia IIC T4 Ga  • DEKRA 20ATEX0133X
UKCA	UK Electromagnetic Compatibility Regulation (2016 No. 1091), compliant with:  • EN 61326-1; Meas./Control/Lab., Industrial Requirements  • EN 61326-2-3; Transducers  • EN 61000-6-2; Industrial Immunity  • EN 61000-6-4; Industrial Emissions  UK Ex Regulation (2016 No. 1107), compliant with:  • EN 60079-0; Explosive Atmospheres, General Requirements  • EN 60079-11; Explosive Atmospheres, Protection "i"  • Ex ia IIC T4 Ga  • DEKRA 20ATEX0133X
CCC Ex	China implementation rules for compulsory product certification explosion-proof electrical products (CNCA-C23-01), compliant with:  • Ex ia IIC T4 Ga  • 2021322315003725
IECEx	Global Ex certificate, compliant with:  • IEC 60079-0; Explosive Atmospheres, General Requirements  • IEC 60079-11; Explosive Atmospheres, Protection "i"  • Ex ia IIC T4 Ga  • IECEX DEK 20.0078X
Ex Entity Parameters	Ui = 26.6V; li = 138 mA; Pi = 0.824 W; Ci = 52 nF; Li = 0 mH

<sup>(1)</sup> See the Product Certification link at rok.auto/certifications for Declarations of Conformity, Certificates, and other certification details.

<sup>(2) 1442-</sup>DRx drivers must be installed in metal enclosures and the 1442-EC-xx extension cables must be installed through metal conduit.

## **1442 Series Catalog Numbers**

Catalog numbers consist of various characters that identify a specific option for the probe system. Use the following tables to determine the catalog number for your probe system.

## **1442 Series Standard Mount Probes**

1442-PS - 05 03 M 00 10 N

а	
Probe Diameter	

Code	Description
05	5 mm (0.20 in.)
08	8 mm (0.31 in.)
11	11 mm (0.43 in.)
18	18 mm (0.71 in.)
25	25.4 mm (1.00 in.)
50	50 mm (1.97 in.)

b						
Body Length	Body Length <sup>(1)</sup>					
	Metric		Imperial			
Code	Description	Code	Description			
03	30 mm	12	1.2 in			
04	40 mm	15	1.5 in			
05	50 mm	16	1.6 in			
07	70 mm	20	2.0 in			
09	90 mm	30	3.0 in			
12	120 mm	40	4.0 in			
15	150 mm	50	5.0 in			
		00	0.0 :			

<sup>(1)</sup> When a body length of 12 is specified, the thread specification of 120 mm (1.2 in.) qualifies the length.

C			
•			

Thread	
Code	Description
М	Metric M8x1 thread (5 mm probe) M10x1 thread (8 mm probe)
E	Imperial 1/4-28 UNF thread (5 mm probe) 3/8-24 UNF thread (8 mm probe)
N	Not threaded (flange mount)

d			
<b>Unthreaded Le</b>	Unthreaded Length		
Code	Description		
	Standard mount probes with a specified unthreaded length are not available.		

е		
Cable Length		
Code	Description	
10	1.0 m (3.28 ft)	
05	0.5 m (1.64 ft)	

f		
Armored Cable Option		
Code	Description	
N	No armor	
А	Armored cable	

#### Standard Mount 5 mm Probes with 1/4-28 UNF Thread and 1.0 m (3.28 ft) Cable

Cat. No.	Description
1442-PS-0512E0010N	5 mm probe tip, standard cable, 1/4-28 UNF thread, 1.2 in. length
1442-PS-0512E0010A	5 mm probe tip, armored cable, 1/4-28 UNF thread, 1.2 in. length
1442-PS-0516E0010N	5 mm probe tip, standard cable, 1/4-28 UNF thread, 1.6 in. length
1442-PS-0516E0010A	5 mm probe tip, armored cable, 1/4-28 UNF thread, 1.6 in. length
1442-PS-0520E0010N	5 mm probe tip, standard cable, 1/4-28 UNF thread, 2 in. length
1442-PS-0520E0010A	5 mm probe tip, armored cable, 1/4-28 UNF thread, 2 in. length
1442-PS-0530E0010N	5 mm probe tip, standard cable, 1/4-28 UNF thread, 3 in. length
1442-PS-0530E0010A	5 mm probe tip, armored cable, 1/4-28 UNF thread, 3 in. length
1442-PS-0540E0010N	5 mm probe tip, standard cable, 1/4-28 UNF thread, 4 in. length
1442-PS-0540E0010A	5 mm probe tip, armored cable, 1/4-28 UNF thread, 4 in. length
1442-PS-0550E0010N	5 mm probe tip, standard cable, 1/4-28 UNF thread, 5 in. length
1442-PS-0550E0010A	5 mm probe tip, armored cable, 1/4-28 UNF thread, 5 in. length
1442-PS-0560E0010N	5 mm probe tip, standard cable, 1/4-28 UNF thread, 6 in. length
1442-PS-0560E0010A	5 mm probe tip, armored cable, 1/4-28 UNF thread, 6 in. length

## Standard Mount 5 mm Probes with M8x1 Metric Thread and 1.0 m (3.28 ft) Cable

Cat. No.	Description
1442-PS-0512M0010A	5 mm probe tip, armored cable, M8x1 thread, 120 mm length
1442-PS-0512M0010N	5 mm probe tip, standard cable, M8x1 thread, 120 mm length
1442-PS-0515M0010A	5 mm probe tip, armored cable, M8x1 thread, 150 mm length
1442-PS-0515M0010N	5 mm probe tip, standard cable, M8x1 thread, 150 mm length
1442-PS-0503M0010A	5 mm probe tip, armored cable, M8x1 thread, 150 mm length
1442-PS-0503M0010N	5 mm probe tip, standard cable, M8x1 thread, 150 mm length
1442-PS-0505M0010A	5 mm probe tip, armored cable, M8x1 thread, 50 mm length
1442-PS-0505M0010N	5 mm probe tip, standard cable, M8x1 thread, 50 mm length
1442-PS-0507M0010A	5 mm probe tip, armored cable, M8x1 thread, 70 mm length
1442-PS-0507M0010N	5 mm probe tip, standard cable, M8x1 thread, 70 mm length
1442-PS-0509M0010A	5 mm probe tip, armored cable, M8x1 thread, 90 mm length
1442-PS-0509M0010N	5 mm probe tip, standard cable, M8x1 thread, 90 mm length

## Standard Mount 8 mm Probes with 3/8-24 UNF Thread and 1.0 m (3.28 ft) Cable

Cat. No.	Description
1442-PS-0812E0010A	8 mm probe tip, armored cable, 3/8-24 UNF thread, 1.2 in. length
1442-PS-0812E0010N	8 mm probe tip, standard cable, 3/8-24 UNF thread, 1.2 in. length
1442-PS-0816E0010A	8 mm probe tip, armored cable, 3/8-24 UNF thread, 1.6 in. length
1442-PS-0816E0010N	8 mm probe tip, standard cable, 3/8-24 UNF thread, 1.6 in. length
1442-PS-0820E0010A	8 mm probe tip, armored cable, 3/8-24 UNF thread, 2 in. length
1442-PS-0820E0010N	8 mm probe tip, standard cable, 3/8-24 UNF thread, 2 in. length
1442-PS-0830E0010A	8 mm probe tip, armored cable, 3/8-24 UNF thread, 3 in. length
1442-PS-0830E0010N	8 mm probe tip, standard cable, 3/8-24 UNF thread, 3 in. length
1442-PS-0840E0010A	8 mm probe tip, armored cable, 3/8-24 UNF thread, 4 in. length
1442-PS-0840E0010N	8 mm probe tip, standard cable, 3/8-24 UNF thread, 4 in. length
1442-PS-0850E0010A	8 mm probe tip, armored cable, 3/8-24 UNF thread, 5 in. length
1442-PS-0850E0010N	8 mm probe tip, standard cable, 3/8-24 UNF thread, 5 in. length
1442-PS-0860E0010A	8 mm probe tip, armored cable, 3/8-24 UNF thread, 6 in. length
1442-PS-0860E0010N	8 mm probe tip, standard cable, 3/8-24 UNF thread, 6 in. length

## Standard Mount 8 mm Probes with 3/8-24 UNF Thread and 0.5 m (1.64 ft) Cable

Cat. No.	Description
1442-PS-0812E0005A	8 mm probe tip, armored cable, 3/8-24 UNF thread, 1.2 in. length
1442-PS-0812E0005N	8 mm probe tip, standard cable, 3/8-24 UNF thread, 1.2 in. length
1442-PS-0816E0005A	8 mm probe tip, armored cable, 3/8-24 UNF thread, 1.6 in. length
1442-PS-0816E0005N	8 mm probe tip, standard cable, 3/8-24 UNF thread, 1.6 in. length
1442-PS-0820E0005A	8 mm probe tip, armored cable, 3/8-24 UNF thread, 2 in. length
1442-PS-0820E0005N	8 mm probe tip, standard cable, 3/8-24 UNF thread, 2 in. length
1442-PS-0830E0005A	8 mm probe tip, armored cable, 3/8-24 UNF thread, 3 in. length
1442-PS-0830E0005N	8 mm probe tip, standard cable, 3/8-24 UNF thread, 3 in. length
1442-PS-0840E0005A	8 mm probe tip, armored cable, 3/8-24 UNF thread, 4 in. length
1442-PS-0840E0005N	8 mm probe tip, standard cable, 3/8-24 UNF thread, 4 in. length
1442-PS-0850E0005A	8 mm probe tip, armored cable, 3/8-24 UNF thread, 5 in. length
1442-PS-0850E0005N	8 mm probe tip, standard cable, 3/8-24 UNF thread, 5 in. length
1442-PS-0860E0005A	8 mm probe tip, armored cable, 3/8-24 UNF thread, 6 in. length

## Standard Mount 8 mm Probes with M10x1 Metric Thread with 1.0 m (3.28 ft) Cable

Cat. No.	Description
1442-PS-0812M0010A	8 mm probe tip, armored cable, M10x1 thread, 120 mm length
1442-PS-0812M0010N	8 mm probe tip, standard cable, M10x1 thread, 120 mm length
1442-PS-0815M0010A	8 mm probe tip, armored cable, M10x1 thread, 150 mm length
1442-PS-0815M0010N	8 mm probe tip, standard cable, M10x1 thread, 150 mm length
1442-PS-0803M0010A	8 mm probe tip, armored cable, m10x1 thread, 30 mm length
1442-PS-0803M0010N	8 mm probe tip, standard cable, M10x1 thread, 30 mm length
1442-PS-0805M0010A	8 mm probe tip, armored cable, M10x1 thread, 50 mm length
1442-PS-0805M0010N	8 mm probe tip, standard cable, M10x1 thread, 50 mm length
1442-PS-0807M0010A	8 mm probe tip, armored cable, M10x1 thread, 70 mm length
1442-PS-0807M0010N	8 mm probe tip, standard cable, M10x1 thread, 70 mm length
1442-PS-0809M0010A	8 mm probe tip, armored cable, M10x1 thread, 90 mm length
1442-PS-0809M0010N	8 mm probe tip, standard cable, m10x1 thread, 90 mm length

### Standard Mount 8 mm Probes with M10x1 Metric Thread with 0.5 m (1.64 ft) Cable

Cat. No.	Description
1442-PS-0812M0005A	8 mm probe tip, armored cable, M10x1 thread, 120 mm length
1442-PS-0812M0005N	8 mm probe tip, standard cable, M10x1 thread, 120 mm length
1442-PS-0815M0005A	8 mm probe tip, armored cable, M10x1 thread, 150 mm length
1442-PS-0815M0005N	8 mm probe tip, standard cable, M10x1 thread, 150 mm length
1442-PS-0803M0005A	8 mm probe tip, armored cable, M10x1 thread, 30 mm length
1442-PS-0803M0005N	8 mm probe tip, standard cable, M10x1 thread, 30 mm length
1442-PS-0805M0005A	8 mm probe tip, armored cable, M10x1 thread, 50 mm length
1442-PS-0805M0005N	8 mm probe tip, standard cable, M10x1 thread, 50 mm length
1442-PS-0807M0005A	8 mm probe tip, armored cable, M10x1 thread, 70 mm length
1442-PS-0807M0005N	8 mm probe tip, standard cable, m10x1 thread, 70 mm length
1442-PS-0809M0005A	8 mm probe tip, armored cable, m10x1 thread, 90 mm length
1442-PS-0809M0005N	8 mm probe tip, standard cable, M10x1 thread, 90 mm length

### Standard Mount 11 mm Probes with 1 m (3.28 ft) Cable

Cat. No.	Description
1442-PS-1116E0510N	11 mm probe tip, standard cable, 1/2-20 UNF thread, 40 mm length
1442-PS-1116E0510A	11 mm probe tip, armored cable, 1/2-20 UNF thread, 40 mm length
1442-PS-1104M0510N	11 mm probe tip, standard cable, M14x1.5 thread, 40 mm length
1442-PS-1104M0510A	11 mm probe tip, armored cable, M14x1.5 thread, 40 mm length

### Standard Mount 18 mm Probes with 1 m (3.28 ft) Cable

Cat. No.	Description
1442-PS-1820E0510A	18 mm probe tip, armored cable, 7/8-14 UNF thread, 50 mm length
1442-PS-1805M0510A	18 mm probe tip, armored cable, M20x1.5 thread, 50 mm length

### Standard Mount 25.4 mm Probes with 1 m (3.28 ft) Cable

Cat. No.	Description
1442-PS-2520E0510A	25.4 mm probe tip, armored cable, 11/4-12 UNF thread, 50 mm length
1442-PS-2505M0510A	25.4 mm probe tip, armored cable, M30x1.5 thread, 50 mm length
1442-PS-2507N0010A	25.4 mm probe tip, armored cable, 4-M6 depth 14 thread, 76 mm length

## Standard Mount 50 mm Probes with 1 m (3.28 ft) Cable

Cat. No.	Description	
1442-PS-5020E0010A	50 mm probe tip, armored cable, 112 UNF thread, 50 mm length	
1442-PS-5005M0010A	50 mm probe tip, armored cable, M24x1.5 thread, 50 mm length	

## **1442 Series Reverse Mount Probes**

1442-PR - 08 30 M 02 05 N a b c d e f

а	
Probe Diameter	
Code Description	
08	8 mm (0.31 in.)

IJ			
Body Length			
	Metric		Imperial
Code	Description	Code	Description
07	70 mm	10	10 in

C	
Thread	
Code	Description
M	Metric M10x1 thread
E	Imperial UNF thread 3/8-24

d	
Unthreaded	Length
Code	Description
02	5.0 mm (0.2 in.)

е	
Cable Length	
Code	Description
05	0.5 m (1.64 ft)
10	1.0 m (3.28 ft)

f	
Armored Cable 0	ption
Code	Description
N	No armor

### Reverse Mount Probes with M10x1 Metric Thread

Cat. No. Description	
1442-PR-0803M0505N	8 mm probe tip, 0.5 m (1.64 ft) integral cable, M10x1 thread, 30 mm length
1442-PR-0803M0510N	8 mm probe tip, 1.0 m (3.28 ft) integral cable, M10x1 thread, 30 mm length

### Reverse Mount Probes with 3/8-24 UNF Thread

Cat. No.	Description	
1442-PR-0812E0205N	8 mm probe tip, 0.5 m (1.64 ft) integral cable, 3/8-24 UNF thread, 1.2 in. length	
1442-PR-0812E0210N	8 mm probe tip, 1.0 m (3.28 ft) integral cable, 3/8-24 UNF thread, 1.2 in. length	

11

### **1442 Series Extension Cables**

1442-EC - 58 40 A

а		
Probe Tip Diameter		
Code	Description	
58	5 mm (0.20 in.) and 8 mm (0.31 in.)	
11	11 mm (0.43 in.)	
18	18 mm (0.71 in.)	
25	25.4 mm (1.00 in.)	
50	50 mm (1.97 in.)	

U	
Cable Length	
Code	Description
40	4.0 m (13.12 ft)
45	4.5 m (14.76 ft)
80	8.0 m (26.25 ft)
85	8.5 m (27.89 ft)

C		
Armored Cable Option		
Code	Description	
N	No armor	
Α	Armored cable	

## Extension Cables for Use with 5 mm and 8 mm Probe Tips

Cat. No.	Description
1442-EC-5840N	4 m (13.12 ft) length
1442-EC-5840A	4 m (13.12 ft) length, armored
1442-EC-5845N	4.5 m (14.76 ft) length
1442-EC-5845A	4.5 m (14.76 ft) length, armored
1442-EC-5880N	8 m (26.25 ft) length
1442-EC-5880A	8 m (26.25 ft) length, armored
1442-EC-5885N	8.5 m (27.89 ft) length
1442-EC-5885A	8.5 m (27.89 ft) length, armored

## Extension Cables for Use with 11 mm Probe Tips

Cat. No.	Description
1442-EC-1140N	4 m (13.12 ft) length
1442-EC-1140A	4 m (13.12 ft) length, armored
1442-EC-1180N	8 m (26.25 ft) length
1442-EC-1180A	8 m (26.25 ft) length, armored

### Extension Cables for Use with 18 mm Probe Tips

Cat. No.	Description			
1442-EC-1840A	4 m (13.12 ft) length, armored			
1442-EC-1880A	8 m (26.25 ft) length, armored			

## Extension Cables for Use with 25.4 mm Probe Tips

Cat. No.	Description			
1442-EC-2540A	4 m (13.12 ft) length, armored			
1442-EC-2580A	8 m (26.25 ft) length, armored			

## Extension Cables for Use with 50 mm Probe Tips

Cat. No.	Description			
1442-EC-5040A	4 m (13.12 ft) length, armored			
1442-EC-5080A	8 m (26.25 ft) length, armored			

### **1442 Series Probe Drivers**

1442-DR - 58 50 a b

a		
Probe Tip Diameter		
Code	Description	
58	5 mm (0.20 in.) and 8 mm (0.31 in.)	
11	11 mm (0.43 in.)	
18	18 mm (0.71 in.)	
25	25.4 mm (1.00 in.)	
50	50 mm (1.97 in.)	

b			
System Length			
Code	Description		
50	5.0 m (16.40 ft)		
90	9.0 m (29.53 ft)		

**IMPORTANT** The probe cable length and the extension cable length, when added, equal the probe system total length.

Probe and Probe Cable		Extension Cable		System Cable Length		Driver <sup>(1)</sup>
0.5 m (1.64 ft)	+	4.5 m (14.76 ft)	=	5.0 m (16.40 ft)	0	1442-DR- <i>xx</i> 50
1.0 m (3.28 ft)	+	4.0 m (13.12 ft)	=	5.0 m (16.40 ft)	0	1442-DR- <i>xx</i> 50
0.5 m (1.64 ft)	+	8.5 m (27.89 ft)	=	9.0 m (29.53 ft)	0	1442-DR- <i>xx</i> 90
1.0 m (3.28 ft)	+	8.0 m (26.25 ft)	=	9.0 m (29.53 ft)	0	1442-DR-xx90

<sup>(1)</sup> Where xx= appropriate code for probe size.

## Probe Drivers for Use with 5 mm and 8 mm Probe Tips

Cat. No.	Description			
1442-DR-5850	Use with 5 m (16.40 ft) total length systems			
1442-DR-5890	Use with 9 m (29.53 ft) total length systems			

### Probe Drivers for Use with 11 mm Probe Tips

Cat. No.	Description			
1442-DR-1150	Use with 5 m (16.40 ft) total length systems			
1442-DR-1190	Use with 9 m (29.53 ft) total length systems			

#### Probe Drivers for Use with 18 mm Probe Tips

Cat. No.	Description
1442-DR-1850	Use with 5 m (16.40 ft) total length systems
1442-DR-1890	Use with 9 m (29.53 ft) total length systems

### Probe Drivers for Use with 25.4 mm Probe Tips

Cat. No.	Description
1442-DR-2550	Use with 5 m (16.40 ft) total length systems
1442-DR-2590	Use with 9 m (29.53 ft) total length systems

## Probe Drivers for Use with 50 mm Probe Tips

Cat. No.	Description
1442-DR-5050	Use with 5 m (16.40 ft) total length systems
1442-DR-5090	Use with 9 m (29.53 ft) total length systems

## **Notes:**

## **Additional Resources**

These documents contain additional information concerning related products from Rockwell Automation.

Resource	Description
Industrial Components Preventive Maintenance, Enclosures, and Contact Ratings Specifications, publication IC-TD002	Provides a quick reference tool for Allen-Bradley® industrial automation controls and assemblies.
Safety Guidelines for the Application, Installation, and Maintenance of Solid-state Control, publication <u>SGI-1.1</u>	Designed to harmonize with NEMA Standards Publication No. ICS 1.1-1987 and provides general guidelines for the application, installation, and maintenance of solid-state control in the form of individual devices or packaged assemblies incorporating solid-state components.
Industrial Automation Wiring and Grounding Guidelines, publication 1770-4.1	Provides general guidelines for installing a Rockwell Automation™ industrial system.
Product Certifications website, <u>rok.auto/certifications</u> .	Provides declarations of conformity, certificates, and other certification details.

You can view or download publications at  $\underline{\mathsf{rok.auto/literature}}$ .

## **Rockwell Automation Support**

Use these resources to access support information.

Technical Support Center	Find help with how-to videos, FAQs, chat, user forums, Knowledgebase, and product notification updates.	rok.auto/support
Local Technical Support Phone Numbers	Locate the telephone number for your country.	rok.auto/phonesupport
Technical Documentation Center	Quickly access and download technical specifications, installation instructions, and user manuals.	rok.auto/techdocs
Literature Library	Find installation instructions, manuals, brochures, and technical data publications.	rok.auto/literature
Product Compatibility and Download Center (PCDC)	Download firmware, associated files (such as AOP, EDS, and DTM), and access product release notes.	rok.auto/pcdc

## **Documentation Feedback**

Your comments help us serve your documentation needs better. If you have any suggestions on how to improve our content, complete the form at rok.auto/docfeedback.

Allen-Bradley, expanding human possibility, and Rockwell Automation are trademarks of Rockwell Automation, Inc. Trademarks not belonging to Rockwell Automation are property of their respective companies.

Rockwell Automation maintains current product environmental compliance information on its website at rok.auto/pec.

Rockwell Otomasyon Ticaret A.Ş. Kar Plaza İş Merkezi E Blok Kat:6 34752, İçerenköy, İstanbul, Tel: +90 (216) 5698400 EEE Yönetmeliğine Uygundur

Connect with us. (7) [7] in [7]









rockwellautomation.com

expanding human possibility

AMERICAS: Rockwell Automation, 1201 South Second Street, Milwaukee, WI 53204-2496 USA, Tel: (1) 414.382.2000, Fax: (1) 414.382.4444 EUROPE/MIDDLE EAST/AFRICA: Rockwell Automation NV, Pegasus Park, De Kleetlaan 12a, 1831 Diegem, Belgium, Tel: (32) 2 663 0600, Fax: (32) 2 663 0640. ASIA PACIFIC: Rockwell Automation, Level 14, Core F, Cyberport 3, 100 Cyberport Road, Hong Kong, Tel: (852) 2887 4788, Fax: (852) 2508 1846 UNITED KINGDOM: Rockwell Automation Ltd. Pitfield, Kiln Farm Milton Keynes, MK11 3DR, United Kingdom, Tel: (44)(1908) 838-800, Fax: (44)(1908) 261-917